

# Incubator

Cat. No.	MO-A01	MO-AOR	MO-AOR-02	MO-ARK	MO-ARC	MO-AVT
Display	Touch screen & graphical interface, 3.5" 64 K color TFT display					
Rotisserie / Speed	N/A	Yes (optional) 5-100rpm	N/A	Yes (optional) 5-100rpm		
Shaker motion	N/A	Orbital clockwise / counterclockwise		Rocking*	Reciprocal	Vortex motion
Shaker speed	N/A	0-200rpm	0-200rpm	5-100rpm	5-100rpm	50-1500rpm
Temperature control range	Ambient +5°C to 85°C					
Temperature uniformity	± 0.2°C at 37°C					
Temperature accuracy	± 0.2°C at 37°C					
Inner chamber dimensions	(WxLxH) 340x225x260 (mm)					
Data logging	RS-232					


\*To perform rocking motion on optional accessories, MO-SEESAW is required.

- User temperature calibration available
- Data logging software for monitoring and recording purposes (optional)
- Timer with alarm function
- Safety door switch device



FC CE

Large color touch screen and graphical control interface for easy access and operation



• Various accessories available

\*Technical specification subject to change without notice.

\*Please visit our website at [www.majorsci.com](http://www.majorsci.com) for more product selection and detailed information.