

## Beakers, low form, Griffin, heavy duty

PYREX®

- Mechanically stronger than standard beakers
- Designed for longer life and increased user safety
- Reinforced rims and spout, less prone to breakage during washing etc.
- Thicker walls and heavier bases
- Manufactured from Pyrex® borosilicate glass
- White graduations and marking spot

Product Code	Capacity (ml)	Height (mm)	O.D. (mm)	Pack qty.
1003-150	150	89	57	12
1003-250	250	90	68	12
1003-400	400	110	77	12
1003-600	600	124	90	6
1003-1L	1000	156	108	6
1003-2L	2000	179	131	4
1003-3L	3000	230	170	1
1003-4L	4000	250	160	1
1003-5L	5000	300	180	1



Graduations are approximate. For advice on the care and use of Pyrex® glassware, please refer to the technical information section.



The thicker walls of Pyrex® Heavy Duty Beakers mean that care must be taken when heating and cooling.



## Beakers, tall form, Berzelius

PYREX®

- Complies with ISO 3819 and DIN 12331
- Manufactured from Pyrex® borosilicate glass
- Printed with Trace Code for downloadable batch certificate
- Batch certificate available to download from [www.scilabware.com](http://www.scilabware.com)
- Tall form with spout
- White graduations and marking spot

Product Code	Capacity (ml)	Height (mm)	O.D. (mm)	Pack qty.
1015/02M	50	70	38	10
1015/04D	100	80	48	10
1015/06D	150	95	54	10
1015/10D	250	120	60	10
1015/14D	400	130	70	10
1015/18D	600	150	80	10
1015/22D	1000	180	95	10
1015/26D	2000	240	120	10



Graduations are approximate.

