



EU Declaration of Conformity

Product	Laboratory Equipment	File Number	P225
Manufacturer	Cole-Parmer Ltd Beacon Road Stone, Staffordshire ST15 0SA United Kingdom		

This declaration of conformity is issued under the sole responsibility of the manufacturer

Object of Declaration

Hotplates and Stirrers
(reference the attached list of catalogue numbers)


The object of the declaration described above is in conformity with the relevant Union Harmonisation Legislation:

Low Voltage Directive	2006/95/EC	(until 19 April 2016)
	2014/35/EU	(from 20 April 2016)
EMC Directive	2004/108/EC	
RoHS Directive	2011/65/EC	

References to the relevant harmonised standards used or references to the other technical specifications in relation to which conformity is declared:

IEC/EN 61010-1:2010	Safety requirements for electrical equipment for measurement, control and laboratory use. Part 1: General requirements.
IEC/EN 61010-2-010:2014	Particular requirements for laboratory equipment for the heating of materials.
IEC/EN 61326-1:2006	Electrical equipment for measurement, control and laboratory use. EMC requirements. Part 1: General requirements (Class A).

Signed for and on behalf of the above manufacturer

Additional Information	Year of CE Marking: 2013
Place of Issue	Stone, Staffordshire, UK
Date of Issue	16 December 2013. Revised 06 February 2017
Authorised Representative	Steve Marriott
Title	Technical Director
Signature	

Range	Catalogue Number	Part Code	Description
UC/US HOT	04805-05	UC151/120V/60	Analogue Stirrer, Ceramic, 150 x 150mm, 120 V
UC/US HOT	04805-06	UC150/120V/60	Undergrad Advanced Analogue Hot Plate, Ceramic, 150 x 150mm, 120 V
UC/US HOT	04805-07	UC151	Analogue Stirrer, Ceramic, 150 x 150mm, 230 V
UC/US HOT	04805-08	UC150	Undergrad Advanced Analogue Hot Plate, Ceramic, 150 x 150mm, 230 V
UC/US HOT	04805-09	UC151/230V/60	Analogue Stirrer, Ceramic, 150 x 150mm, 230 V, 60 Hz
UC/US HOT	04805-11	US151/120V/60	Analogue Stirrer, Stainless Steel, 150 x 150mm, 120 V, 60 Hz
UC/US HOT	04805-12	US150/120V/60	Undergrad Advanced Analogue Hot Plate, Aluminium, 150 x 150mm, 120 V
UC/US HOT	04805-13	US151	Analogue Stirrer, Stainless Steel, 150 x 150mm, 230 V
UC/US HOT	04805-14	US150	Undergrad Advanced Analogue Hot Plate, Aluminium, 150 x 150mm, 230 V
UC/US HOT	04805-15	US151/230V/60	Analogue Stirrer, Stainless Steel, 150 x 150mm, 230 V, 60 Hz
UC/US HOT	04805-56	UC152/120V/60	Advanced Analogue Stirring Hot Plate, Ceramic, 150 x 150mm, 120 V
UC/US HOT	04805-58	UC152	Advanced Analogue Stirring Hot Plate, Ceramic, 150 x 150mm, 230 V
UC/US HOT	04805-64	US152/120V/60	Advanced Analogue Stirring Hot Plate, Aluminium, 150 x 150mm, 120 V
UC/US HOT	04805-66	US152	Advanced Analogue Stirring Hot Plate, Aluminium, 150 x 150mm, 230 V
UC/US HOT	04805-68	US152/220V	Advanced Analogue Stirring Hot Plate, Aluminium, 150 x 150mm, 220 V, 60 Hz
UC/US HOT	04805-80	UC152D/120V/60	Advanced Digital Stirring Hot Plate, Ceramic, 150 x 150mm, 120 V
UC/US HOT	04805-82	UC152D/220V	Advanced Digital Stirring Hot Plate, Ceramic, 150 x 150mm, 220 V, 60 Hz
UC/US HOT	04805-84	UC152D	Advanced Digital Stirring Hot Plate, Ceramic, 150 x 150mm, 230 V
UC/US HOT	04805-86	US152D/120V/60	Advanced Digital Stirring Hot Plate, Aluminium, 150 x 150mm, 120 V
UC/US HOT	04805-88	US152D/220V	Advanced Digital Stirring Hot Plate, Aluminium, 150 x 150mm, 220 V, 60 Hz
UC/US HOT	04805-90	US152D	Advanced Digital Stirring Hot Plate, Aluminium, 150 x 150mm, 230 V