

## Tri-Cornered Beakers

### I. APPLICATIONS

1. Transfer of chemicals and other liquids

### II. FEATURES

1. Materials: Strong, medical-grade polypropylene
2. Chemically resistant to alcohols and mild organic solvents
3. Transparent wall permits easy viewing of tube contents
4. Autoclavable

### III. BEAKER DESIGN

1. Unique three-corner design
2. Available in 50ml, 100ml, 250ml, 400ml, 800ml and 1,000ml
3. Molded graduations
4. Clearly visible with either clear or turbid samples

### IV. PACKAGING

1. Bulk Packaging, 25 pieces/sleeve and 4 sleeves/case

### V. DESCRIPTION

| Item    | Size           | Packaging                        | Sterile |
|---------|----------------|----------------------------------|---------|
| 93-0050 | 50ml Beaker    | 25 pieces/sleeve, 4 sleeves/case | No      |
| 93-0100 | 100ml Beaker   | 25 pieces/sleeve, 4 sleeves/case | No      |
| 93-0250 | 250ml Beaker   | 25 pieces/sleeve, 4 sleeves/case | No      |
| 93-0400 | 400ml Beaker   | 25 pieces/sleeve, 4 sleeves/case | No      |
| 93-0800 | 800ml Beaker   | 25 pieces/sleeve, 4 sleeves/case | No      |
| 93-1000 | 1,000ml Beaker | 25 pieces/sleeve, 4 sleeves/case | No      |

### VI. STERILITY

1. N/A

### VII. CERTIFICATION

Biologix products are manufactured completely according to the TUV ISO 9001:2008 standard.

### VIII. RESTRICTIONS

Refer to the Chemical Resistance Chart in our catalog, and available within our online catalog.

**IX. PRODUCT PARAMETER**

Dimensions=mm

| Cat #   | Description | A     | B     | C         | D         | E         | F    | G     |
|---------|-------------|-------|-------|-----------|-----------|-----------|------|-------|
| 93-0050 | Beaker      | 67    | 58    | O.D. 31.1 | O.D. 43.1 | O.D. 46.9 | 31   | 57    |
| 93-0100 | Beaker      | 84    | 72    | O.D. 38.7 | O.D. 53.7 | O.D. 58.4 | 39   | 71    |
| 93-0250 | Beaker      | 101   | 88    | O.D. 49.1 | O.D. 68   | O.D. 74   | 49   | 88    |
| 93-0400 | Beaker      | 114.7 | 99.9  | O.D. 52   | O.D. 82   | O.D. 84   | 55.6 | 110.3 |
| 93-0800 | Beaker      | 133.1 | 115.2 | O.D. 65   | O.D. 104  | O.D.105.1 | 65   | 137   |
| 93-1000 | Beaker      | 140.6 | 121.7 | O.D. 71.6 | O.D.112.7 | O.D.114.1 | 70.9 | 143   |

