

Easy to Use

High Performance

Great Low Price

SALINITY CHECKER!!

Digital Hand-held "Pocket" Salinity Refractometer

PAL-06S

Cat.No.4406



Actual size

Features

- * Calibration with water only
- * Measurement in 3 seconds
- * Extremely water resistant (IP65)
- * Light & Compact, 100g
- * Ergonomically designed for easy, one-handed operation
- * Convenient storage case
- * Automatic Temperature Compensation (ATC)
- * Designed with a strap holder option

Specifications

Measurement Range	Salinity 0~100‰
Resolution	Salinity 1‰
Measurement Accuracy	Salinity $\pm 2\%$
Measurement Temperature	10.0~40.0°C (ATC)
Sample Volume	0.3ml or more
Measurement Time	3 seconds
Power Supply	AAA alkaline battery $\times 2$
Battery Life	Approx. 11,000 measurements (Using a new alkaline battery)
International Protection Class	IP65 Water Resistant
Dimensions and Weight	55 (W) \times 31 (D) \times 109 (H) mm, 100g (Main unit only)

All ATAGO refractometers are designed and manufactured in Japan.

HACCP G.M.P. G.L.P.

ATAGO products are acknowledged by HACCP, G.M.P. and G.L.P.

ATAGO CO.,LTD.

Headquarters: 32-10, Honcho, Itabashi-ku, Tokyo 173-0001 Japan
TEL: 81-3-3964-6156 FAX: 81-3-3964-6137
overseas@atago.net <http://www.atago.net/>

ATAGO U.S.A., Inc.

12011 NE First Street, Bldg. C, Suite 110 Bellevue, WA 98005 U.S.A.
TEL: 1-425-637-2107 FAX: 1-425-637-2110
customerservice@atago-usa.com <http://www.atago.net/>

ATAGO INDIA Instruments Pvt. Ltd.

A-501, Mangal Aarambh Business Centre, Near Kora Kendra, Off. S.V. Road, Borivali (West), Mumbai-400 092 India
TEL: 91-22-2833-8038 / 8076 FAX: 91-22-2899-8164
customerservice@atago-india.com



※Specifications and appearance are subject to change without notice.