

**Mini Cooler**

Cat. No.	MC-0201	MC-0203
Display	LCD	
Power	40W	60W
Unit Dimension	W185x L152 x H134 mm (excluding lid)	
Controller	High performance 32 bits microprocessor	
Heating /Cooling Chamber	Molded water-proof aluminum alloy coated with PTFE	
Temp Control Range	30°C below ambient temperature (minimum -10°C)	30°C below ambient temperature (minimum -10°C) to 100°C
Temp Uniformity	± 0.2°C at 37°C	
Temp Accuracy	± 0.25°C at 37°C	
Temp Calibration	Yes	
Cooling/ Heating Rate	Max. 5.5°C/ 6°C per min	
Cooling/ Heating Parts	Peltier	Peltier/ Heating element
Safety Device	Leak proof heating chamber	
Operating Temperature	Ambient to 40° C	
Block Material	Aluminum alloy	
Data Log	USB	