

Weighing Boats

Flexible polystyrene boats feature smooth surfaces to provide accurate pour-outs with minimal sample loss

- Select white, black, or blue for best color contrast to ensure sample is completely removed
- Biologically inert and resistant to dilute and weak acids, aqueous solutions, alcohols, and bases
- Temperature range -10 to 70°C (14 to 158°F)
- Can be used with microwave moisture analyzers
- **All are FDA/food-grade compliant**
- **Disposable**



Smooth surfaces provide accurate pour-outs




Manufactured and packaged in a clean room



Standard weighing boats	Regular Material Part No.	Antistatic Material Part No.	Size	L x W x H	Qty.	Color
	HS1420A	HS1420AA	Small	46 x 46 x 8 mm	500/pk	White <input type="checkbox"/>
	HS1420B	HS1420BB	Medium	85 x 85 x 24 mm	500/pk	White <input type="checkbox"/>
	HS1420C	HS1420CC	Large	140 x 140 x 22 mm	500/pk	White <input type="checkbox"/>
	HS1421A	HS120222	Small	46 x 46 x 8 mm	500/pk	Blue <input checked="" type="checkbox"/>
	HS1421B	HS120223	Medium	85 x 85 x 24 mm	500/pk	Blue <input checked="" type="checkbox"/>
	HS1421C	HS120224	Large	140 x 140 x 22 mm	500/pk	Blue <input checked="" type="checkbox"/>
	HS1423A	HS1423AA	Small	46 x 46 x 8 mm	500/pk	Black <input checked="" type="checkbox"/>
	HS1423B	HS1423BB	Medium	85 x 85 x 24 mm	500/pk	Black <input checked="" type="checkbox"/>
	HS1423C	HS1423CC	Large	140 x 140 x 22 mm	500/pk	Black <input checked="" type="checkbox"/>

- Boats are shallow with a wide, flat bottom to resist tipping
- Rounded corners simplify transfer



Hexagonal weighing boats	Regular Material Part No.	Antistatic Material Part No.	Size	L x W x H	Qty.	Color
	—	HS14251A	Small	38 x 25 x 9 mm	500/pk	White <input type="checkbox"/>
	—	HS14251B	Medium	64 x 51 x 19 mm	500/pk	White <input type="checkbox"/>
	—	HS14251C	Large	102 x 76 x 22 mm	500/pk	White <input type="checkbox"/>
	—	HS14251D	X-Large	127 x 89 x 31 mm	500/pk	White <input type="checkbox"/>

- Bend flexible boats at points to form pour spouts
- Flat bottoms and sloping sides provide accurate transfer



Pour-boat weighing dishes	Regular Material Part No.	Antistatic Material Part No.	Size	L x W x H	Qty.	Color
	HS1419A	HS120225	Small	43 x 58 x 13 mm	500/pk	White <input type="checkbox"/>
	HS1419B	HS120226	Medium	83 x 132 x 26 mm	500/pk	White <input type="checkbox"/>
	HS1419C	HS120227	Large	108 x 183 x 26 mm	500/pk	White <input type="checkbox"/>

- Pour-spout design easily dispenses samples without flexing the dish
- Flat-bottom dishes are made from 12-mil thick polystyrene for better strength, stability, and handling



Square weighing boats	Regular Material Part No.	Antistatic Material Part No.	Size	L x W x H	Qty.	Color
	HS1422	—	Medium	90 x 90 x 7 mm	500/pk	White <input type="checkbox"/>

- Shallow boat with a wide, flat bottom to resist tipping
- Ideal for solid product weighing



Diamond weighing boats	Regular Material Part No.	Antistatic Material Part No.	Size	L x W x H	Qty.	Color
	HS1424AA	HS1425AA	5 mL	55 x 35 x 6 mm	500/pk	White <input type="checkbox"/>
	HS1424A	HS1425A	25 mL	71 x 46 x 14 mm	500/pk	White <input type="checkbox"/>
	HS1424B	HS1425B	30 mL	78 x 56 x 14 mm	500/pk	White <input type="checkbox"/>
	HS1424C	HS1425C	100 mL	119 x 90 x 19 mm	500/pk	White <input type="checkbox"/>
	HS1427AA	HS1426AA	5 mL	55 x 35 x 6 mm	500/pk	Black <input checked="" type="checkbox"/>
	HS1427A	HS1426A	25 mL	71 x 46 x 14 mm	500/pk	Black <input checked="" type="checkbox"/>
	HS1427B	HS1426B	30 mL	78 x 56 x 14 mm	500/pk	Black <input checked="" type="checkbox"/>
	HS1427C	HS1426C	100 mL	119 x 90 x 19 mm	500/pk	Black <input checked="" type="checkbox"/>

- Diamond shape that easily flexes for accurate pouring
- Wide, flat bottom to resist tipping

Flexible boats bend to form pour spout