

## EP-2158 | RUNONE™ SYSTEM, TIMER AND MULTICASTER, BLUE, 200-240V

includes: EP-2002, EP-1139, EP-1010, EP-1001, EP-1019



### RunOne Tank, Qty:1

Catalog Number: EP-2002

Material: White Polycarbonate

### RunOne Power Supply, Qty:1

Catalog Number: EP-1139, RunOne Power Supply with Timer

Material: White Polycarbonate

Dimensions: LxWxH: 19 cm x 12.5 cm x 5.5 cm (7.5" x 5" x 2.25")

Maximum Voltage Input: 120VAC, 60Hz

Over Current Limit: 300mA

Power Rating: 70W

Electrical Rating: 120VAC, 60Hz, 70W, 600mA

### Transformer, Qty:1

Catalog Number: EP-1010

Voltage Input: 230V~ 50Hz 60VA

Voltage Output: 120V~ 50Hz 50VA

### RunOne Casting System, Qty:1

Catalog Number: EP-1001

Casting Stand Material: White Polycarbonate

Tray Material: Clear Polycarbonate w/ Black Print

Mini Trays: 5.4(w) x 5.9(l)cm, Qty:4

Landscape Trays: 10.9(w) x 5.9(l)cm, Qty:2

Combs - 1mm thick: 6 and 8 wells for Mini; 12 and 17 wells for Landscape; Qty:2

Load Volume: 28µl for 6 and 12 well, 17µl for 8 and 17 wells

### MultiCaster System, Qty:1

Catalog Number: EP-1019, Blue MultiCaster System

Material: Blue Polycarbonate

Casting Stand: Blue Casting Stand, 12 Slots, Qty:1

Gel Tray: Long UV Transparent 11.7(w) x 11.9(l)cm (EP-1025), Qty:1

Combs: Blue 8+1(30µl)/16+2 (11µl), 1mm, Qty:6

MultiChannel Compatible: Yes, 8 Channel Compatible

Visualization Plate: Red Long Plate 11.5(w) x 11.9(l)cm (EP-1029), Qty:1

Gel Size: 11.7(w) x 11.9(l) cm