

Characteristics:

Binder-free micro-glass fibre filter paper.

Applications:

Pre-filter for membrane filtration.
Filtration of suspended solids in water.
Waste water analysis.

Benefits:

Temperature resistant to about 500°C.
Increased loading capacity for fine particle filtration.
Suitable for filtration of larger volumes.

Physical properties	Method	Units	Typical value
Basis weight	ISO 536	g/m ²	143
Thickness	ISO 534	µm	700
Filtration speed (initial)	ISO 1924-3	s/50 ml H ₂ O	105
Penetration (0.3 µm at 5.3 cm/s)	EN 143	%	<0.001

2018-01-11; Version 2.

All indicated data to be understood as typical

Contact office:

Ahlstrom-Munksjö Falun AB
Box 1003
SE-791 10 Falun
Sweden
T: +46 23 705880
E-mail: CS.Falun@ahlstrom-munksjo.com