

TECHNICAL DATA SHEET

Part Nbr	036326
Designation	Grade GF/D glass microfiber prefilter



Description :

- ✓ Application : Highly suitable for use in applications involving air filtration and for gravimetric analysis of volatile materials where ignition is involved. Because of the low resistance it is recommended for fluid flow and high particle loading capacity
- ✓ Grade : GF/D
- ✓ Diameter : 47 mm
- ✓ Nominal thickness : 675 μm
- ✓ Nominal basis weight : 121 g/m^2
- ✓ Max recommended temperature : 550 $^{\circ}\text{C}$
- ✓ Material : Borosilicate glass
- ✓ Binder type : Binder Free
- ✓ Format : circles

Sales unit :

100 Grade GF/D glass microfiber prefilter