

# DATA SHEET

**Gr. 0263**

## •DESIGNATION

- Glass microfibres filter
- Material: 100% glass fibres
- Binder: no

## •APPLICATIONS

- Staining of dyed papers
- Purification filtration
- Solvent filtration
- Sample filtration (HPLC)
- Cells collection

## •TECHNICAL SPECIFICATIONS

Characteristics	Values	Unities	Standards
Weight	75 (+/- 5%)	g/sqm	150536
Thickness	0,45	mm	
Filtration velocity	}	sec.	DIN 53137
		310 sec.	Herzberg
Pore size	0,7	µm	
Burst strength	50	kPa	interne