

Fillers and Bulbs

1 Latex Dropper Bulbs

- Designed for use with Pasteur pipettes, small pipettes, and medicine droppers

2 Dropper Bulbs

- Designed for use with Pasteur pipettes, small pipettes, and medicine droppers

3 Rubber Bulbs

- Contoured shape and heavy-wall neck increase grip for easier use with pipettes and syringes

4 Vacuum/Pressure Bulb

- Ideal for gas sampling or for pumping gas through apparatus
- Two rubber valves with PVC connections (tubing not supplied)



5 Safety Bulb Pipette Filler

- Features a white ABS attachment containing a silicone conical adapter that seals around pipettes without twisting
- Pipette does not contact hard plastic, which reduces the risk of cracking and chipping
- Elastic band for hanging on reagent bottle or wrist
- Filler fits standard size pipettes

6 Pipette Filler

- Efficient one-handed operation
- Control air- evacuation, liquid uptake, and liquid dispensing with three valves
- Pinch release-valve for smooth liquid flow
- Red pipette filler is safe for pipetting of caustics and does not contain carbon black and will not smudge

Latex Dropper Bulbs (Natural Rubber)

Pack of 72

| Item No. | Color | Volume mL | Length in | Length mm | Outer Diameter in | Outer Diameter mm | Hole Diameter in | Hole Diameter mm |
|----------|--------|-----------|-----------|-----------|-------------------|-------------------|------------------|------------------|
| HS20622A | Yellow | 1 | 1.7 | 43 | 0.51 | 13 | 0.20 | 5 |
| HS20622B | | 2 | 2.0 | 52 | 0.51 | 13 | 0.24 | 6 |

Dropper Vial Bulbs (Silicone Rubber)

Pack of 24

| Item No. | Color | Volume mL | Length in | Length mm | Outer Diameter in | Outer Diameter mm | Hole Diameter in | Hole Diameter mm |
|----------|-------|-----------|-----------|-----------|-------------------|-------------------|------------------|------------------|
| HS20629A | Blue | 1 | 1.1 | 28.7 | 0.47 | 12 | 0.24 | 6.0 |
| HS20629B | | 3 | 1.6 | 41 | 0.70 | 17.8 | 0.26 | 6.5 |

Rubber Bulbs (Natural Rubber)

| Item No. | Color | Volume mL | Length in | Length mm | Outer Diameter in | Outer Diameter mm | Hole Diameter in | Hole Diameter mm |
|----------|-------|-----------|-----------|-----------|-------------------|-------------------|------------------|------------------|
| HS20630A | | 12 | 2.0 | 51 | 1.3 | 34 | 0.16 | 4 |
| HS20630B | | 15 | 1.9 | 50 | 1.3 | 34 | 0.16 | 4 |
| HS20630C | Red | 30 | 2.6 | 66 | 1.8 | 46 | 0.24 | 6 |
| HS20630D | | 60 | 3.1 | 80 | 2.1 | 54 | 0.24 | 6 |
| HS20630E | | 150 | 4.1 | 103 | 2.9 | 73 | 0.24 | 6 |

Vacuum/Pressure Bulb (Natural Rubber)

| Item No. | Color | Volume mL | Length in | Length mm | Outer Diameter in | Outer Diameter mm | Hole Diameter in | Hole Diameter mm |
|----------|-------|-----------|-----------|-----------|-------------------|-------------------|------------------|------------------|
| HS20631B | Black | 85 | 4.2 | 106 | 2.1 | 52 | 0.29 | 7.4 |

Safety Bulb Pipette Filler (Natural Rubber)

Pack of 3

| Item No. | Color | Volume mL | Length in | Length mm | Outer Diameter in | Outer Diameter mm | Hole Diameter in | Hole Diameter mm |
|----------|-------|-----------|-----------|-----------|-------------------|-------------------|------------------|------------------|
| HS20623 | Red | 15 | 4.2 | 106 | 1.6 | 41 | 0.39 | 10 |

Pipette Filler (Natural Rubber)

| Item No. | Color | Volume mL | Length in | Length mm | Outer Diameter in | Outer Diameter mm | Hole Diameter in | Hole Diameter mm |
|----------|-------|-----------|-----------|-----------|-------------------|-------------------|------------------|------------------|
| HS20632A | Black | | | | | | | |
| HS20632B | Red | 35 | 5.1 | 130 | 2.1 | 54 | 0.24 | 6.0 |
| HS20632C | Blue | | | | | | | |