

RF1000™

manual pipette controller

Lightweight and easy to use

The RF1000™ is a manual pipette controller uniquely designed for one-handed operation. Simply squeeze the main bulb and push the toggle forward to aspirate or back to dispense. Push the blowout bulb to expel any liquid remaining in the pipette.

- Tapered silicone rubber pipette adapter allows a large range of pipette sizes (1-50 mL) and makes to be used. Replaceable when worn.
- Accepts common and readily available replacement filters unlike other pipette aids whose filters are custom. This will help reduce total cost of ownership over time
- Includes one 0.45 µm filter

Part No.	Description
HS1000RFU	RF1000 with magnetic/mountable holder
Replacement parts	
HS5000RFFIL	Replacement filters, pack of 5
HS5000RFRP	Replacement pipette adapter, Silicone
HS1000RFRR	Replacement nose cone, PP, Dark Blue

Specifications	
Power:	Manual
Filter:	PTFE/25 mm dia / 0.45 µm filter in PP housing
Pipettes:	1 – 50 mL, glass and plastic
Pipette Nozzle:	Polypropylene, autoclavable
Dimensions:	180 x 45 x 120 mm



Operate with one hand

