

Product Data Sheet for KLEENGUARD\* A40 Liquid & Particle Protection Coveralls - Hooded / White

Product Information

<b>Customer Facing Code</b>	97900 - 97950
<b>Description</b>	KLEENGUARD* A40 Liquid & Particle Protection Coveralls - Hooded / White
<b>PDS Reference</b>	31/10/2017
<b>Status</b>	On Sale



Packaging Configuration

<b>Case Contents</b>	25 Garments
<b>Outer Pack Material</b>	Paper
<b>Commodity Code</b>	62101098

Packaging and Palletisation

Code/Size	ITF Barcode	EAN Barcode	Case LWH (cm)	Net/Gross Weight (kg)	Pallet Type	Pallet LWH (m)	Cases per Pallet	Inner Gross Weight (Kg)
97900-S	10036000097907	036000097900	40 x 30 x 34	5.45/6.64	E5	1.20 x 0.80 x 1.17	8 x 3 =24	
97910-M	10036000097914	0360000979172	40 x 30 x 34	6.95/8.04	E5	1.20 x 0.80 x 1.17	6 x 3 =18	
97920-L	10036000097921	036000097924	40 x 30 x 36	7.15/8.26	E5	1.20 x 0.80 x 1.23	6 x 3 =18	
97930-XL	10036000097938	036000097931	40 x 30 x 36	7.73/8.84	E5	1.20 x 0.80 x 1.23	6 x 3 =18	
97940-XXL	10036000097945	036000097948	40 x 30 x 39	8.01/9.15	E5	1.20 x 0.80 x 1.31	6 x 3 =18	
97950-XXXL	10036000097952	036000097955	40 x 30 x 39	8.31/9.55	E5	1.20 x 0.80 x 1.32	6 x 3 =18	

Product Description

Single-use breathable protective clothing to improve safety and comfort in high-risk areas providing general protection against water-based or chemical splashes, liquids or dust particles with added benefit of antistatic protection.

Ideal for: providing high levels of protection against larger particles, radioactive dust and chemical splashes; helping to reduce contamination in low lint and critical areas; working in pharmaceutical industries, manufacturing, utilities, electronics, agriculture and paint spraying areas.

Available as: white, anti-static, silicone-free coveralls in sizes S to XXXL, with specially designed hood to fit a respirator, full-length zip, strong over-locked stitched seams and double-layer fabric for comfort, safety and strength, each coverall supplied in a sealed clear polybag.

# Product Data Sheet for KLEENGUARD\* A40 Liquid & Particle Protection Coveralls - Hooded / White

## Features and Benefits

Features	Benefits
Approved as Complex Design (Category 3) equipment	Offering protection to the levels specified for Type 5 & 6 by CEN
Ideal for protecting against powders, larger fibres and protection against a wide range of chemicals	Reducing contamination in critical areas, Working in working in pharmaceutical industries, manufacturing, utilities, electronics
Suitable for use as protection against solid particles and particulate radioactive contamination	EN1073-2
Treated to be antistatic	To EN 1149-5
Ultra low lint fabric	Suitable for tasks such as paint spraying cars and clean room environments

## Product Configuration



Technology	Film laminate	Low lint	Yes
Breatheable	No	Sterile	No
Latex Free	Yes	Silicone Free	Yes
Colour	White	Lightweight	No

## International Standards and Symbols




### Marketing

Technology – Apparel	Fabric Choice	
----------------------	---------------	---





### Solution

Safer Workplace	We know staff safety is your top priority. You can rely on our solutions to protect them, their environment and your important work.	
Productive Workplace	The success of your business hinges on your work efficiency. That's why our solutions are designed to help improve your productivity.	


## Standard R+E

EN ISO 13982-1:2004 - Particle Protection	Workwear Type 5	
EN 13034:2005 – Limited Splash Protection	Workwear Type 6	
EN 1073-2:2002	Radioactive Dust Contamination Protection	

# Product Data Sheet for KLEENGUARD\* A40 Liquid & Particle Protection Coveralls - Hooded / White

<b>Chemical Protection</b>	Chemical Protection	
<b>EN 1149-1:1995</b>	Antistatic	
<b>CE Mark</b>	Simple - CAT I, Intermediate - CAT II or Complex - CAT III	
<b>Range Symbol</b>	Apparel	

## Trade

<b>ISO 9001</b>	This gives the requirements for quality management systems, is now firmly established as the globally implemented standard for providing assurance about the ability to satisfy quality requirements and to enhance customer satisfaction in supplier-customer relationships.	 <b>ISO 9001:2008</b>
-----------------	---	--

## Test Results

Test	Result
-EN ISO 13935-2 Seam Strength (Grab test)	Class 3 of 6
EN ISO 13982-2 - Particle Inward Leakage (taped at the hood, wrist & ankles)	PASS
EN1149-5 - Antistatic	PASS
BS EN 863:1996 - Puncture resistance	Class 2 of 6
EN 1073-2 - Radioactive dust	Class 1
EN 13274-4 M3 - Resistance to Ignition	PASS
EN 530 M2 - Abrasion Resistance	Class 6 of 6
EN ISO 13934-1 - Tensile Strength	Class 2 of 6
EN ISO 17491-4 (modified) - Resistance to Penetration by Liquids (spray test)	PASS
EN ISO 7854 MB - Flex Cracking	Class 4 of 6
ISO 6530 - Repellency to Liquid Chemicals	10%NaOH , 30%H2SO4, Class 3 of 3
ISO 6530 - Resistance to Penetration by Liquid Chemicals	10%NaOH , 30%H2SO4, Class 3 of 3
ISO 9073-4 - Trapezoidal Tear Resistance	Class 2 of 6

## Packaging

<b>Unit Of Sale</b>	Case	<b>Max Weight(kg)</b>	10.51
<b>Case Dimension(LXWXH)(cm)</b>	40 x 30 x 39	<b>Inner Pack Material</b>	Plastic

# Product Data Sheet for KLEENGUARD\* A40 Liquid & Particle Protection Coveralls - Hooded / White

## Instructions

Do not use chlorine - based bleach.



Do not dry clean.



Inflammable. Keep away from open flames, sparks or intense heat sources. The fabric will begin to melt at the approximate temperature indicated.



The open book pictogram - indicates that the user should read and understand the USER INSTRUCTIONS before using the garment.



Do not iron.



Do not tumble dry



Do not wash.



## Information

It is the employer's responsibility to assess the risk of the task to be undertaken and determine the correct choice of personal protective equipment for the task. The manufacturer, Kimberly-Clark, does not accept any responsibility for the incorrect choice or misuse of the personal protective equipment shown in this brochure. All care has been taken to ensure that the information contained herein is as accurate as possible at the time of publication, however errors may occur and legislation concerning personal protective equipment is under constant review and may change in the lifetime of this brochure. Accordingly, the specification for the products may be subject to change. We would advise you to contact INFOFAX if you have any queries concerning the products shown or the suitability of such products for a particular task. Always dispose of used protective equipment in a safe and appropriate manner in accordance with European, National and Local environmental regulations.

### Infobox Details

infofax@kcc.com

### Websites

www.kcprofessional.co.uk

### Storage conditions

Keep dry. Store in a cool dry place and shield from exposure to direct sunlight, intense artificial light or exposure to sources of radiation or ozone.

### Durability

This product has an unlimited shelf life.

### Customer Service Number

For more information please contact Customer Service during regular office hours-0870 551 044

### Country of Origin

CHINA