

## Product Data Sheet for JACKSON SAFETY\* G40 Foam Coated Gloves - Hand Specific / Blue

### Product Information

|                             |   |
|-----------------------------|---|
| <b>Customer Facing Code</b> | 40225 - 40229   |
| <b>Description</b>          | JACKSON SAFETY* G40 Foam Coated Gloves - Hand Specific / Blue |
| <b>PDS Reference</b>        | 02/08/2017  |
| <b>Status</b>               | On Sale   |



### Packaging Configuration

|                            |                              |
|----------------------------|------------------------------|
| <b>Case Contents</b>       | 5 Bags x 12 Pairs = 60 Pairs |
| <b>Outer Pack Material</b> | Paper                        |
| <b>Commodity Code</b>      | 61161020                     |

### Packaging and Palletisation

| Code/Size | ITF Barcode    | EAN Barcode  | Case LWH (cm)      | Net/Gross Weight (kg) | Pallet Type | Pallet LWH (m)     | Cases per Pallet | Inner Gross Weight (Kg) |
|-----------|----------------|--------------|--------------------|-----------------------|-------------|--------------------|------------------|-------------------------|
| 40225-7   | 10036000402251 | 036000402254 | 41 x 25.2 x 12.9   | 2.16/2.79             | E5          | 1.20 x 0.80 x 1.31 | 6 x 9 =54        |                         |
| 40226-8   | 10036000402268 | 036000402261 | 41.4 x 25.6 x 13.7 | 2.28/2.91             | E5          | 1.20 x 0.80 x 1.38 | 6 x 9 =54        |                         |
| 40227-9   | 10036000402275 | 036000402278 | 41.4 x 25.6 x 13.7 | 2.64/3.27             | E5          | 1.20 x 0.80 x 1.38 | 6 x 9 =54        |                         |
| 40228-10  | 10036000402282 | 036000402285 | 41.4 x 25.6 x 13.7 | 3/3.63                | E5          | 1.20 x 0.80 x 1.38 | 6 x 9 =54        |                         |
| 40229-11  | 10036000402299 | 036000402292 | 41.4 x 25.6 x 13.7 | 3.48/4.11             | E5          | 1.20 x 0.80 x 1.38 | 6 x 9 =54        |                         |

### Product Description

A range of Gloves to protect hands against mechanical hazards, get the job done safely and help reduce costs.

Ideal for: providing PPE category 2 protection in mechanical, manufacturing and construction environments, without breaking or tearing; allowing sensitive touch for handling small parts.

Available as: pairs of hand specific gloves in a choice of five sizes with colour-coded cuffs, with foam Nitrile coated palms for excellent dry grip and seamless knitted nylon backing, offering breathability and comfort.

### Features and Benefits

| Features                          | Benefits  |
|-----------------------------------|---|
| <b>EU Abrasion Rating of 4</b>    | Better durability, Key measurement on EU scale, Highest score on EU scale   |
| <b>Excellent Dexterity</b>        | Results in improved productivity  |
| <b>Excellent Wet and Dry Grip</b> | Results in improved productivity, Good grip for light oil applications (better protection), Lowers chance of dropping things in material handling |



# Product Data Sheet for JACKSON SAFETY\* G40 Foam Coated Gloves - Hand Specific / Blue

## Product Configuration



|                             |                 |                     |               |
|-----------------------------|-----------------|---------------------|---------------|
| <b>Sterile</b>              | No              | <b>Latex Free</b>   | Yes           |
| <b>Main Protection Type</b> | General purpose | <b>Application</b>  | Industrial    |
| <b>Ambidextrous</b>         | No              | <b>Powdered</b>     | No            |
| <b>Material</b>             | Nylon           | <b>Coated</b>       | Palm Coated   |
| <b>Liner</b>                | Y - Other       | <b>Coating</b>      | Nitrile       |
| <b>Colour</b>               | Blue            | <b>Coating Type</b> | Coated        |
| <b>Gauge</b>                | 15              | <b>Glove Shape</b>  | Hand Specific |
| <b>Length</b>               | 160 - 240 mm    |                     |               |

## International Standards and Symbols


### Solution

|                             |   |   |
|-----------------------------|---|---|
| <b>Safer Workplace</b>      | We know staff safety is your top priority. You can rely on our solutions to protect them, their environment and your important work.  |  |
| <b>Productive Workplace</b> | The success of your business hinges on your work efficiency. That's why our solutions are designed to help improve your productivity. |  |

### Standard R+E

|                    |  |   |
|--------------------|--|---|
| <b>EN 388:2003</b> | This standard which is designed to assess the performance of a fabric or layers of fabric for their ability to resist mechanical risks of abrasion, blade cut, tear and puncture. The test procedure includes a separate test for each of these properties, and a performance level is awarded according to each test result. This standard is only applicable in conjunction with EN420 |  |
| <b>CE Mark</b>     | Simple - CAT I, Intermediate - CAT II or Complex - CAT III   |  |

### Trade

|                 |   |   |
|-----------------|---|---|
| <b>ISO 9001</b> | This gives the requirements for quality management systems, is now firmly established as the globally implemented standard for providing assurance about the ability to satisfy quality requirements and to enhance customer satisfaction in supplier-customer relationships. |  |
|-----------------|---|---|

### Packaging

|                                  |                    |                            |       |
|----------------------------------|--------------------|----------------------------|-------|
| <b>Unit Of Sale</b>              | Case               | <b>Max Weight(kg)</b>      | 4.52  |
| <b>Case Dimension(LXWXH)(cm)</b> | 41.4 x 25.6 x 13.7 | <b>Inner Pack Material</b> | Paper |

### Instructions

The open book pictogram - indicates that the user should read and understand the USER INSTRUCTIONS before using the garment.



Protect from heat and radioactive sources.



Keep Dry. Store in a cool, dry place.



5 cycles of washing in a domestic machine with standard cleaning agents @ 40°C



# Product Data Sheet for JACKSON SAFETY\* G40 Foam Coated Gloves - Hand Specific / Blue

## Information

It is the employer's responsibility to assess the risk of the task to be undertaken and determine the correct choice of personal protective equipment for the task. The manufacturer, Kimberly-Clark, does not accept any responsibility for the incorrect choice or misuse of the personal protective equipment shown in this brochure. All care has been taken to ensure that the information contained herein is as accurate as possible at the time of publication, however errors may occur and legislation concerning personal protective equipment is under constant review and may change in the lifetime of this brochure. Accordingly, the specification for the products may be subject to change. We would advise you to contact INFOFAX if you have any queries concerning the products shown or the suitability of such products for a particular task. Always dispose of used protective equipment in a safe and appropriate manner in accordance with European, National and Local environmental regulations.

**Infobox Details**

infofax@kcc.com

**Websites**

www.kcprofessional.co.uk

**Storage conditions**

Keep dry. Store in a cool dry place and shield from exposure to direct sunlight, intense artificial light or exposure to sources of radiation or ozone.

**Durability**

This product has a five years shelf life from the date of manufacture.

**Customer Service Number**

For more information please contact Customer Service during regular office hours-0870 551 044

**Country of Origin**

PAKISTAN