



## TECHNICAL DATA SHEET

### **PRODUCT DESCRIPTION**

<b>PRODUCT CODE</b>	168C
<b>GENERAL DESCRIPTION</b>	TAMPONE SECCO A/TWISTED1000PKG
<b>DETAILED DESCRIPTION</b>	10 BOXES CONTAINING 100 TWISTED ALLUMINIUM APPLICATORS IN TUBE

### **PRODUCT COMPONENTS**

<b>APPLICATOR</b>	TWISTED ALLUMINIUM APPLICATOR	<b>DIMENSIONAL SPECIFICATIONS</b>
		<p>LENGHT OF THE ALLUMINIUM SHAFT: 150 mm ± 2 mm          ALLUMINIUM TIP DIAMETER: 0,50 mm ± 0,10 mm          STICK DIAMETER HANDLE PART: 0,50 mm ± 0,10 mm          FIBRE TIP LENGTH: 15 mm ± 1 mm          FIBRE TIP DIAMETER: 2,5 mm ± 0.2 mm          TOTAL LENGHT: 151 mm ± 2 mm</p>
<b>CAP</b>	CAP	<b>DIMENSIONAL SPECIFICATIONS</b>
		<p>EXTERNAL DIAMETER: 12.0 mm ± 1.0 mm          CAP LENGTH: 32.0 mm ± 1.0 mm</p>
<b>TRANSPORT TUBE</b>	TUBE	<b>DIMENSIONAL SPECIFICATIONS</b>
		<p>EXTERNAL DIAMETER: 12 mm ± 0,5 mm          INTERNAL DIAMETER: 9.0 mm ± 0.5 mm          TUBE LENGTH: 155 mm ± 1 mm</p>



## TECHNICAL DATA SHEET

### **PACKAGING SPECIFICATION**

<b>INNER BOX QTY</b>	100
<b>OUTER BOX QTY</b>	1000
<b>PACKAGING</b>	BULK

### **IMPORTANT INFO**

<b>STERILIZATION METHOD</b>	GAMMA IRRADIATION
<b>STORAGE TEMPERATURE</b>	5/25°C-DO NOT FREEZE
<b>SHELF LIFE</b>	36 MONTHS