


# Ultrasonic cleaner

Accessories: wire baskets for ultrasonic cleaner WUC-A and WUC-N


## Stainless steel wire baskets for ultrasonic cleaner WUC-A

For device	Capacity	Measurements	Article	Order number
WUC-A02H	1.8 l	120x105xh65 mm	B02	<b>DH.WUC.B02</b>
WUC-A03H	3.3 l	215x115xh65 mm	B03	<b>DH.WUC.B03</b>
WUC-A06H	6 l	247x123xh96 mm	B06	<b>DH.WUC.B06</b>
WUC-A10H	10 l	262x206xh93 mm	B10	<b>DH.WUC.B10</b>
WUC-A22H	22 l	452x263xh93 mm	B22	<b>DH.WUC.B22</b>



## Stainless steel wire baskets for ultrasonic cleaner WUC-N

For device	Capacity	Measurements	Article	Order number
WUC-N30H	30 l	340x240xh150 mm	Ba7021	<b>DH.Ba7021</b>
WUC-N47H	47 l	390x290xh200 mm	Ba7022	<b>DH.Ba7022</b>
WUC-N60H	60 l	440x340xh200 mm	Ba7023	<b>DH.Ba7023</b>
WUC-N74H	74 l	490x390xh200 mm	Ba7024	<b>DH.Ba7024</b>



DOMINIQUE DUBOIS