

rpm measuring instrument

testo 465 – Non-contact rpm
measurement

Easy one-hand operation

Storage of mean/min./max. values as well as last
measurement value

Measurement distance up to 600 mm

Robust design thanks to SoftCase (protective cover)



rpm

With the testo 465, you can measure rpm easily without contact using only one hand. The measuring instrument is thus suitable for measurements on rotating parts such as ventilators and shafts. Simply attach a reflective marker (optional) to the measurement object, point the visible red beam of light at the reflective marker, and measure. The

distance to the measurement object is up to 600 mm. The measuring instrument stores mean, min. and max. values as well as the last measurement value. The SoftCase included in delivery protects the instrument from impact, ensuring an especially long working life.

Technical data / Accessories

testo 465

testo 465 RPM measuring instrument with transport case incl. reflectors and batteries

Part no. 0563 0465



Sensor type **Optically with mod. light beam**

Measuring range	+1 to +99999 rpm
Accuracy ±1 digit	±0.02% of m.v.
Resolution	0.01 rpm (+1 to +99.99 rpm) 0.1 rpm (+100 to +999.9 rpm) 1 rpm (+1000 to +99999 rpm)

General technical data

Operating temperature	0 to +50 °C
Storage temperature	-20 to +70 °C
Battery type	2 AA batteries or rech. battery
Display	5-figure LCD display, 1-line
Weight	145 g
Warranty	2 years
Dimensions	144 x 58 x 20 mm
Battery life	40 h

Accessories

Part no.

Accessories for measuring instrument

Reflectors, self-adhesive (1 pack = 5 off, each 150 mm long)	0554 0493	
ISO calibration certificate/rpm optical and mechanical rpm measuring instruments; cal. points 500; 1000; 3000 rpm	0520 0012	
ISO calibration certificate/rpm optical rpm measuring instruments; calibration points 10; 100; 1000; 10000; 99500 rpm	0520 0022	
ISO calibration certificate/rpm Calibration points freely selectable from 10 to 99500 rpm	0520 0114	
DAkkS calibration certificate/rpm Optical rpm probes, 3 points in instrument measurement range (1 to 99999 rpm)	0520 0422	