

# Sound level measuring instrument

testo 815

---

Frequency evaluation according to characteristic curves A and C

---

Easy to adjust

---

Maximum and minimum store

---

Switchable time evaluation Fast/Slow

---



The testo 815 is the ideal instrument for the evaluation of sound level in everyday work. The instrument can be used for monitoring measurements in the areas of air conditioning or heating, on combustion plants or at workplaces, however machine or discotheque noise can also be evaluated quickly and precisely.

Using the Fast/slow button, the measurement time can be set from 1 s to 125 ms, in order to better evaluate the noise source. The frequency analysis can also be switched from characteristic curve A to C. The characteristic curve A corresponds to the sound pressure perception of the human

ear, whereas characteristic curve C can also evaluate the low-frequency components of a sound.

With the help of the optional calibrator, the measuring instrument can be recalibrated directly on site with the screwdriver provided. The wind protection cap included in delivery ensures correct measurement results when measuring outdoors, and if required can protect the microphone from dirt and dust.

## Technical data / Accessories

### testo 815

testo 815, sound level meter incl. calibration  
screwdriver, wind screen and battery

Part no. 0563 8155



#### Technical data testo 815

Measuring range	+32 to +130 dB
Frequency range	31.5 Hz to 8 kHz
Accuracy ±1 digit	±1.0 dB
Resolution	0.1 dB
Operating temperature	0 to +40 °C
Storage temperature	-10 to +60 °C
Battery type	9V block battery
Battery life	70 h
Weight	195 g
Dimensions	255 x 55 x 43 mm
Warranty	2 years
Section meas. ranges: 30 to 80 dB; 50 to 100 dB; 80 to 130 dB Time weighting: FAST 125 ms setting / SLOW 1 s setting Pressure dependency: -0.0016 dB/hPa	

#### Technical data sound level calibrator

Battery type	9V block battery
Battery life	40 h
Warranty	2 years
Accuracy	±0.5 dB in accordance with Class 2 to IEC 60942
Sound pressure level: 94 dB/104 dB, switchable Frequency: 1000 Hz Also suitable for ½ and 1 inch microphones by other manufacturers	

#### Accessories

#### Part no.

#### Accessories for measuring instrument

Calibrator, for regular calibration of testo 815, testo 816, testo 816-1	0554 0452	
ISO calibration cert./sound pressure; calibration point 94 dB at different frequencies	0520 0111	
ISO calibration certificate sound pressure calibrators	0520 0411	

