

Temperature measuring instrument (1-channel)

testo 925 – For fast and reliable measurements in the HVAC field



Ideally suited to applications in the HVAC field

1-channel temperature measuring instrument with optional wireless probes

TopSafe, the indestructible protective case, protects from dirt and impact

Continuous display of min/max values

Audible alarm (adjustable limit values)

Hold-button for freezing measurement values

Large, backlit display

The testo 925 is a 1-channel temperature measuring instrument which is particularly suitable for applications in the HVAC field. The instrument is optimum for the connection of fast and reliable thermocouple probes. Using measurement data transfer by radio, the measurement value of a further temperature probe can be additionally displayed wirelessly. The protective cover TopSafe ensures water- and dirt-proofness when a probe is connected. The

instrument reliably and continuously displays the minimum and maximum measurement values. The measurement values shown in the display (current measurement value, frozen measurement value, or the minimum/maximum values) can be printed out via the Testo report printer (optional). The user can store limit values in the instrument himself; as soon as these upper and lower values are violated, an audible signal sounds.

Technical data

testo 925

testo 925, 1 channel temperature measuring instrument T/C Type K, audible alarm, connection of an optional radio probe, with battery and calibration protocol

Part no. 0560 9250



Sensor type	Type K (NiCr-Ni)
Measuring range	-50 to +1000 °C
Accuracy ±1 digit	±(0.5 °C +0.3% of m.v.) (-40 to +900 °C) ±(0.7 °C +0.5% of m.v.) (remaining range)
Resolution	0.1 °C (-50 to +199.9 °C) 1 °C (remaining range)

General technical data

Operating temperature	-20 to +50 °C
Storage temperature	-40 to +70 °C
Housing material	ABS
Battery type	9V block battery, 6F22
Battery life	200 h (connected probe, backlight off) 45 h (radio mode, backlight off) 68 h (connected probe, backlight always on) 33 h (radio mode, backlight always on)
Dimensions	182 x 64 x 40 mm
Weight	171 g
Warranty	2 years



Optional protective case TopSafe



Wireless measurement with radio probes



1 probe connection

Accessories


Accessories for measuring instrument	Part no.
9V rech. battery for instrument, instead of battery	0515 0025
Recharger for 9V rechargeable battery for external recharging of 0515 0025 battery	0554 0025
Radio module for upgrading measuring instrument with radio option	
Radio module for measuring instrument, 869.85 MHz, approval for the countries: DE, FR, UK, BE, NL, ES, IT, SE, AT, DK, FI, HU, CZ, PL, GR, CH, PT, SI, MT, CY, SK, LU, EE, LT, IE, LV, NO	0554 0188
Radio module for measuring instrument, 915,00 MHz FSK, approval for USA, CA, CL	0554 0190
Printer and Accessories	
Testo fast printer IrDA with wireless infrared interface; 1 roll thermal paper; 4 AA batteries	0554 0549
Spare thermal paper for printer (6 rolls), permanent ink measurement data documentation legible for up to 10 years	0554 0568
Transport and Protection	
TopSafe, protects from impact and dirt	0516 0221
Service case for measuring instrument, probe and accessories, dimensions 454 x 316 x 111 mm	0516 1200
Service case for measuring instrument and probe, dimensions 454 x 316 x 111 mm	0516 1201
Case for measuring instrument and probes	0516 0210
Other features	
Handle for attachable measurement tips, applicable for all Testo probes with miniature thermocouple plugs	0409 1092
Extension cable, 5m, for thermocouple probe Type K	0554 0592
Silicone heat paste (14g), Tmax = +260°C, improves heat transfer in surface probes	0554 0004
Calibration Certificates	
ISO calibration certificate/temperature for air/immersion probes, calibration points -18°C; 0°C; +60°C	0520 0001
ISO calibration certificate/temperature (Applies only to immersion/penetration probe 0602 2693) meas. instr. with air/immersion probe; cal. points 0°C; +150°C; +300°C	0520 0021
ISO calibration certificate/temperature meas. instr. with air/immersion probe; calibration points 0°C; +300°C; +600°C	0520 0031
ISO calibration certificate/temperature meas. instr. with surface probe; calibration points +60°C; +120°C; +180°C	0520 0071
DAkKS calibration certificate/temperature meas. instr. with air/immersion probe; calibration points -20 °C; 0 °C; +60 °C	0520 0211
DAkKS calibration certificate/temperature contact surface temperature probes; calibration points +100°C; +200°C; +300°C	0520 0271

Radio probes

Radio handles with probe head for air-/ immersion-penetration-meas.

Part no.


Radio handle for plug-in probe heads, incl. T/C adapter, approval for the countries: DE, FR, UK, BE, NL, ES, IT, SE, AT, DK, FI, HU, CZ, PL, GR, CH, PT, SI, MT, CY, SK, LU, EE, LT, IE, LV, NO; Radio freq. 869,85 MHz FSK	0554 0189
T/C probe head for air/immersion/penetration measurement (T/C Type K)	0602 0293
Radio handle for plug-in probe heads, incl. T/C adapter, approval for USA, CA, CL; Radio freq. 915.00 MHz FSK	0554 0191
T/C probe head for air/immersion/penetration measurement (T/C Type K)	0602 0293

Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	Resolution	t ₉₉
 100 mm 30 mm Ø 5 mm Ø 3,4 mm	-50 to +350 °C Short-term to +500 °C	Radio handle: ±(0,5 °C +0,3% of m.v.) (-40 to +500 °C) ±(0,7 °C +0,5% of m.v.) (remaining range) T/C probe head: Class 2	0,1 °C (-50 to +199,9 °C) 1,0 °C (remaining range)	t ₉₉ (in water) 10 s

Radio handles with probe head for surface measurement

Part no.


Radio handle for plug-in probe heads, incl. T/C adapter, approval for the countries: DE, FR, UK, BE, NL, ES, IT, SE, AT, DK, FI, HU, CZ, PL, GR, CH, PT, SI, MT, CY, SK, LU, EE, LT, IE, LV, NO; Radio freq. 869,85 MHz FSK	0554 0189
T/C probe head for surface measurement (T/C Type K)	0602 0394
Radio handle for plug-in probe heads, incl. T/C adapter, approval for USA, CA, CL; Radio freq. 915.00 MHz FSK	0554 0191
T/C probe head for surface measurement (T/C Type K)	0602 0394

Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	Resolution	t ₉₉
 120 mm 40 mm Ø 5 mm Ø 12 mm	-50 to +350 °C Short-term to +500 °C	Radio handle: ±(0,5 °C +0,3% of m.v.) (-40 to +500 °C) ±(0,7 °C +0,5% of m.v.) (remaining range) T/C probe head: Class 2	0,1 °C (-50 to +199,9 °C) 1,0 °C (remaining range)	5 s

Radio handles for attachable T/C probes

Part no.

Radio handle for plug-in probe heads, incl. T/C adapter, approval for the countries: DE, FR, UK, BE, NL, ES, IT, SE, AT, DK, FI, HU, CZ, PL, GR, CH, PT, SI, MT, CY, SK, LU, EE, LT, IE, LV, NO ; Radio freq. 869,85 MHz FSK	0554 0189
Radio handle for plug-in probe heads, incl. T/C adapter, approval for USA, CA, CL; Radio freq. 915,00 MHz FSK	0554 0191

Illustration	Measuring range	Accuracy	Resolution
	-50 to +1000 °C	±(0,7 °C +0,3% of m.v.) (-40 to +900 °C) ±(0,9 °C +0,5% of m.v.) (remaining range)	0,1 °C (-50 to +199,9 °C) 1,0 °C (remaining range)

Technical data Radio probes

Radio immersion/penetration probe, NTC

Battery type	2 x 3V button cell (CR 2032)
Battery life	150 h (meas. rate 0,5 s) 2 months (meas. rate 10 s)

Radio handle

Battery type	2 x 3V button cell (CR 2032)
Battery life	215 h (meas. rate 0,5 s) 6 months (meas. rate 10 s)

Common Technical Data

Measuring rate	0,5 s or 10 s, adjustable on handle
Radio coverage	Up to 20 m (without obstructions)
Radio transmission	Unidirectional
Operating temperature	-20 to +50 °C
Storage temperature	-40 to +70 °C

Probes

Probe type	Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	t ₉₉	Part no.
Air probes					
<ul style="list-style-type: none"> Robust air probe, T/C Type K, Fixed cable 1.2 m 		-60 to +400 °C	Class 2 ¹⁾	200 s	0602 1793
Immers./penetr. probes					
<ul style="list-style-type: none"> Efficient and fast-action immersion probe, waterproof, TC Type K, Fixed cable 1.2 m 		-60 to +1000 °C	Class 1 ¹⁾	2 s	0602 0593
<ul style="list-style-type: none"> Fast-action, waterproof immersion/penetration probe, TC Type K, Fixed cable 1.2 m 		-60 to +800 °C	Class 1 ¹⁾	3 s	0602 2693
Immersion tip, flexible, TC Type K		-200 to +1000 °C	Class 1 ¹⁾	5 s	0602 5792
Immersion measurement tip, flexible, for measurements in air/exhaust gases (not suitable for measurements in smelters), TC Type K		-200 to +1300 °C	Class 1 ¹⁾	4 s	0602 5693
<ul style="list-style-type: none"> Waterproof immersion/penetration probe, TC Type K, Fixed cable 1,2 m 		-60 to +400 °C	Class 2 ¹⁾	7 s	0602 1293
Surface probes					
<ul style="list-style-type: none"> Fast-reaction paddle surface probe, for measurements in inaccessible places, e.g. narrow apertures and slots, TC Type K, Fixed cable 		0 to +300 °C	Class 2 ¹⁾	5 s	0602 0193
<ul style="list-style-type: none"> Fast-action surface probe with sprung thermocouple strip, also for uneven surfaces, measurement range short-term to +500°C, TC Type K, Fixed cable 1.2 m 		-60 to +300 °C	Class 2 ¹⁾	3 s	0602 0393
<ul style="list-style-type: none"> Waterproof surface probe with widened measurement tip for flat surfaces, T/C Type K, Fixed cable 1.2 m 		-60 to +400 °C	Class 2 ¹⁾	30 s	0602 1993

◆ The measuring instrument inside TopSafe is waterproof with this probe.

1) According to standard EN 60584-2, the accuracy of Class 1 refers to -40 to +1000 °C (Type K), Class 2 to -40 to +1200 °C (Type K), Class 3 to -200 to +40 °C (Type K). A probe always corresponds to only one accuracy class.






Probes

Probe type	Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	t ₉₉	Part no.
Surface probes					
<ul style="list-style-type: none"> Fast-action surface probe with sprung thermocouple strip, bent, also for uneven surfaces, measurement range short-term to +500 °C, TC Type K, Fixed cable 1.2 m 		-60 to +300 °C	Class 2 ¹⁾	3 s	0602 0993
<ul style="list-style-type: none"> Efficient, waterproof surface probe with small measurement head for flat surfaces, TC Type K, Fixed cable 1.2 m 		-60 to +1000 °C	Class 1 ¹⁾	20 s	0602 0693
Flat head surface probe with telescopic handle max. 680 mm for measurements at hard-to-access points, TC Type K, Fixed cable 1.6 m (correspondingly shorter when telescope extended)		-50 to +250 °C	Class 2 ¹⁾	3 s	0602 2394
Magnetic probe, adhesive force approx. 20 N, with magnets, for measurements on metal surfaces, TC Type K, Fixed cable 1.6 m		-50 to +170 °C	Class 2 ¹⁾	150 s	0602 4792
Magnetic probe, adhesive force approx. 10 N, with magnets, for higher temp., for measurements on metal surfaces, TC Type K, Fixed cable		-50 to +400 °C	Class 2 ¹⁾		0602 4892
Pipe wrap probe with velcro strip; for temperature measurement on pipes with diameter up to max. 120 mm; Tmax. +120 °C; TC Type K, Fixed cable		-50 to +120 °C	Class 1 ¹⁾	90 s	0628 0020
Pipe wrap probe for pipe diameter 5 to 65 mm, with exchangeable measuring head. Meas. range short-term up to +280 °C, TC Type K, Fixed cable		-60 to +130 °C	Class 2 ¹⁾	5 s	0602 4592
Spare meas. head for pipe wrap probe, TC Type K		-60 to +130 °C	Class 2 ¹⁾	5 s	0602 0092
Clamp probe for measurements on pipes, pipe diameter 15 to 25 mm (max. 1 ¹⁾), meas. range short-term up to +130 °C, TC Type K, Fixed cable		-50 to +100 °C	Class 2 ¹⁾	5 s	0602 4692

◆ The measuring instrument inside TopSafe is waterproof with this probe.

1) According to standard EN 60584-2, the accuracy of Class 1 refers to -40 to +1000 °C (Type K), Class 2 to -40 to +1200 °C (Type K), Class 3 to -200 to +40 °C (Type K). A probe always corresponds to only one accuracy class.

Probes

Probe type	Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	t ₉₉	Part no.
Food probes					
◆ Waterproof food probe made of stainless steel (IP65), TC Type K, Fixed cable		-60 to +400 °C	Class 2 ¹⁾	7 s	0602 2292
Waterproof robust immersion/penetration probe with metal protection hose Tmax +230°C, e.g. for monitoring temp. in cooking oil, T/C Type K, Fixed cable		-50 to +230 °C	Class 1 ¹⁾	15 s	0628 1292
Thermocouples					
Thermocouple with TC adapter, flexible, 800 mm long, fibre glass, TC Type K		-50 to +400 °C	Class 2 ¹⁾	5 s	0602 0644
Thermocouple with TC adapter, flexible, length 1500 mm, fibreglass, TC Type K		-50 to +400 °C	Class 2 ¹⁾	5 s	0602 0645
Thermocouple with TC adapter, flexible, 1500 mm long, PTFE, TC Type K		-50 to +250 °C	Class 2 ¹⁾	5 s	0602 0646

◆ The measuring instrument inside TopSafe is waterproof with this probe.
 1) According to standard EN 60584-2, the accuracy of Class 1 refers to -40 to +1000 °C (Type K), Class 2 to -40 to +1200 °C (Type K), Class 3 to -200 to +40 °C (Type K). A probe always corresponds to only one accuracy class.

Information on surface measurement:

- The response times t₉₉ stated are measured on ground steel or aluminium plates at +60 °C.
- The stated accuracies are sensor accuracies.
- The accuracy in your application is dependent on the surface structure (roughness), material of the measurement object (heat capacity and heat transfer), as well as sensor accuracy. Testo creates a corresponding calibration certificate for the deviations of your measurement system in your application. For this purpose, Testo uses a surface test bench developed in cooperation with the PTB (Physikalisch Technische Bundesanstalt).



DOMINIQUE DUTSCHER SAS

0981 9314/msp/06.2017

Subject to change without notice.