

1- glass door tall safety cabinet Type 30

COMPLIANCE

EN 14470-1 FM 6050

ADVANTAGES

- 30-minute fire resistant and made in France
- EN 14470-1 and FM 6050 compliant
- Storage of flammables

BUT ALSO...

- Thermo-expanding seals of the doors
- Holes for the connection to the ventilation
- Normalized labelling provided with the equipment
- Adjustable leveling feet for enhance stability
- Pedestal area under-driveable by a forklift by removing panel
- Tested and approved according to FM 6050
- Glass doors for an immediate view of the products



TECHNICAL FEATURES

Model	3034PVE	Door closure	self-closing
Compliance	EN 14470-1 FM 6050	Shipping dimensions HxWxD (mm)	2180 x 1200 x 800
Cabinet materials	Melamine wood structure	Ventilation	Both inlet and outlet on the top of the cabinet
Doors color	light grey RAL 7035	Openings diameter (mm)	100
Number of doors	1	Number of compartments	1
Doors type	swing doors	Containment sump	1
Hinges	right	HS Code	94032080

COMPLEMENTARY ACCESSORIES - VENTILATION AND FILTRATION BOXES

- Filtration box with activated carbon filter for organic vapors (Réf : CDF-A)
- Ventilation box for a connection to the outside (Réf : CDV-A)
- Recycling air box Labopur - NF X 15-211 (Réf : HS0C)
- Connecting kit (Réf : KRC)

OPTIONS

- Containment sump for 1-door cabinets Types 30, 60 & 90 (Réf : B148)
- Perforated cover plate for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : C148)
- Retention shelf for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : E48)
- Containment sump in PVC for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : SB148)
- Protection shelf in PVC for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : SE148)
- Sliding drawer for 1-door or multirisk safety cabinets Types 30, 60 & 90 (Réf : T148)

Model	External dimensions HxWxD (mm)	Internal dimensions HxWxD (mm)	Storage capacity (L)	Containment sump	Shelves	Load capacity	Weight (kg)
3034PVE	1980 x 605 x 550	1580 x 495 x 420	130	1	3	30	117.00