

ClearLine® Pipette Controller

Description

- Designed for cordless work with 0.5-100 ml glass or plastic pipettes.
- Lightweight handle, smooth pushbuttons and switches ensure effortless pipetting even during extensive use.
- Different operational modes may be selected depending on pipetting volume and viscosity of liquid.
- 2 Liquid aspiration speeds HIGH or LOW, while dispensing can be by gravity (GRAV) or supported by the pump (BLOW).
- PTFE 0.2µm filter protects the unit against overfilling.
- The powerful re-chargeable Ni-MH battery allows many hours of continuous work.
- Supplied with a charging stand & wall mount for convenient charging and storage.
- Rest wings allows practical storage during operation.

Technical specification

- Volume Range: 0.5–100 ml
- Working/Recharging Temperature 10–35 °C
- Storage Temperature -25 to 50 °C
- NiMH Battery AA type 1300 mAh, 2*1 2,4 V
- Autoclavable nosepiece at 121 °C

Packaging:

- White glossy box with label or white box with sleeve
- Instruction manual
- Universal charger 9V with set of plugs: EU, US, UK, AU
- Wall hanger
- • Charging stand
- • PTFE 0.2µm filter

Product Attributes

