

ORBi-SHAKER™ CO₂

Remote Controlled, All Environment Shakers

The new Orbi-Shaker CO₂ series is designed for shaking, mixing & aeration applications in extreme environments, including CO₂ incubators. It can withstand temperatures from 0 to 65°C and humidity levels up to 100%.

To avoid contamination, unintentional release of gas or deviations from protocol, all settings are adjusted via the included remote control module. This module can be stored outside of the chamber and connects to the shaker via a flat (1mm thickness) cable, that easily passes through a port or underneath an incubator door without compromising the seal. This allows for user adjustment of run time or mixing speed without opening the chamber door(s).

The instrument is supplied with a non-slip rubber mat platform. In addition, convenient MAGIC Clamp™ platforms (of multiple sizes) are also available for use with Erlenmeyer flasks and test tube racks. The unique magnetic attachment method has been widely recognized as the easiest way to instantly change between flask clamps of different sizes.



Item: BT4000

Compatibility Chart:	Thermo® HeraCell™		New Brunswick™		Shel Lab® 142L & 167L	Nuair™ 4750, 4850, 4950, 5800	Fisher® IsoTemp™ 184	WVR® Symphony™	
	150	240	Galaxy® S41i	Galaxy® 170				5.3A	8.5A
Orbi-Shaker CO ₂ (14 x 12" platform)	●	●	●	●	●	●	●	●	●
Orbi-Shaker CO ₂ XL (16 x 16.5" platform)	●	●	N/A	●	●	●	●	●	●
Orbi-Shaker CO ₂ XL (18 x 18 platform)	N/A	●	N/A	N/A	●	●	●	N/A	●

N/A Not Compatible
 ● Compatible
 ● Compatible, Maximizes Capacity



Remote controller adjusts shaker settings from outside of the chamber and magnetically attaches to most incubators.

Ordering Information

BT4000* Orbi-Shaker CO₂, Shaker with remote control, includes 13x12" non-slip platform, 115V

BT4010* Orbi-Shaker CO₂ XL, Shaker with remote control, includes 16x16.5" non-slip platform, 115V

*To order item in 230V, add (-E) to item number.

Technical Data

Speed Range: 30 to 300 rpm
 Speed Increment: 1 rpm
 Orbit: 19mm
 Max. Capacity:
 BT4000: 2 x 2L or 5 x 1L Flasks
 BT4010: 5 x 2L or 9 x 1L Flasks
 Platform Dimensions:
 Included with BT4000: 13 x 12 in. / 33 x 30 cm
 Included with BT4010: 16 x 16.5 in. / 40.5 x 42 cm
 Ambient Operating Temp: 0° to 65°C
 Weight:
 BT4000: 25 lbs / 11.3 kg
 BT4010: 50lbs / 22.7 kg
 Dimensions:
 BT4000 Shaker: 11.9 x 13.4 x 3.5 in.
 30 x 34 x 9 cm
 BT4010 Shaker: 17 x 18 x 5 in.
 43 x 45.75 x 12.7 cm
 Cord Length: 60.5 in. / 154 cm
 Electrical: 115V Or 230V, 50-60Hz*

Optional - Universal Platforms

BT3000-MR MAGIC Clamp universal platform for BT4000 (14x12")
 BT4010-MR MAGIC Clamp universal platform for BT4010 (16x16.5")
 H1010-MR MAGIC Clamp universal platform for BT4010 (18x18")

Flask & Tube Rack Accessories for MAGIC Clamp Platforms

H1000-MR-50 Flask Clamp, 50ml (BT4000: max. 30 / BT4010: max. 49*)
 H1000-MR-125 Flask Clamp, 125ml (BT4000: max. 20 / BT4010: max. 36*)
 H1000-MR-250 Flask Clamp, 250ml (BT4000: max. 14 / BT4010: max. 25*)
 H1000-MR-500 Flask Clamp, 500ml (BT4000: max. 9 / BT4010: max. 16*)
 H1000-MR-1000 Flask Clamp, 1000ml (BT4000: max. 5 / BT4010: max. 9*)
 H1000-MR-2000 Flask Clamp, 2000ml (BT4000: max. 2 / BT4010: max. 5*)
 H1000-MR-1550 Tube Rack, 12x50 & 21x15 ml tubes (BT4000: max.2 / BT4010: max. 4*)
 H1000-MR-T15 Tube Rack, 32x15 tubes (BT4000: max. 3 / BT4010: max. 8*)
 H1000-MR-T50 Tube Rack, 15x50 tubes (BT4000: max. 3 / BT4010: max. 8*)
 H1000-MR-T600 Bottle Rack, 4x500/600ml conical bottles (BT4000: max. 2 / BT4010: max. 4*)

*Maximum capacity listed for the BT4010 with the optional H1010-MR MAGIC Clamp Platform.

Benchmark Scientific

PO Box 709 Edison, NJ 08818
 Phone: 908-769-5555 Fax: 732-313-7007
 Web: www.BenchmarkScientific.com
 Email: Info@BenchmarkScientific.com