


Benchmark 


# INCU-SHAKER *Series*

## Shaking Incubators

- + *Exceptional temperature uniformity*
- + *Miniature and cooling options available*
- + *Exchange flask clamps in one second with the new **MAGiC CLAMP™** magnetic system*



**INCU-SHAKER™ Mini**




**INCU-SHAKER™ 10L**


WITH  
**MAGiC**  
**CLAMP**










**Incu-Shaker 10L/LR**  
(H2010/H2012)



**Incu-Shaker Mini**  
(H1001-M)



### Technical Data:

Temperature Range (Mini):	Ambient +5 to 70°C (Increments of 0.1°C)
Temperature Range (10L):	Ambient +5 to 60°C (Increments of 0.1°C)
Temperature Range (10LR):	Ambient -12 to 60°C (Increments of 0.1°C)
Temperature Uniformity:	+/- 0.25 %
Temperature Accuracy:	+/- 0.1 %
Shaking Speed Range:	30 to 300 rpm (Increments of 1 rpm)
Shaking Orbit:	19 mm (3/4")
Platform Dimensions:	
Incu-Shaker Mini	9.5 x 11.5 in. / 23.5 x 29.2 cm
Incu-Shaker 10L/LR	17.8 x 17.8 / 45 x 45 cm
Exterior Dimensions:	
Incu-Shaker Mini	11 x 18.8 x 13 in. / 28 x 48 x 33 cm
Incu-Shaker 10L	20 x 26 x 19 in. / 51 x 65 x 47 cm
Incu-Shaker 10LR	20 x 31 x 22 in. / 51 X 79 X 56 cm.
Weight:	
Incu-Shaker Mini	25 lbs. / 11.5 kg
Incu-Shaker 10L	120 lbs / 55 kg
Incu-Shaker 10LR	170 lbs / 78 kg
Electrical:	120 or 230V, 50-60Hz

### Ordering Information

H1001-M*	Incu-Shaker Mini, includes standard rubber mat platform, 115V
H2010*	Incu-Shaker 10L, includes standard rubber mat platform, 115V
H2012*	Incu-Shaker 10LR, includes standard rubber mat platform, 115V

\*To order an item in 230V, add (-E) to item number.

### Optional Platforms and Shelves

H1000-MR	MAGic Clamp universal platform, for Incu-Shaker Mini (9.5 x 11.5")
H1010-MR	MAGic Clamp universal platform, for Incu-Shaker 10L/LR (18 x 18")
H1000-P-MP	Microplate platform, 4 position for Incu-Shaker Mini
H1010-P-MP	Microplate platform, 6 position for Incu-Shaker 10L/LR
H1000-P-SP	Spring rack platform, holds uncommon vessels for Incu-Shaker Mini
H1010-P-SP	Spring rack platform, holds uncommon vessels for Incu-Shaker 10L/LR
H1010-SH	Optional Shelf, for Petri Dishes, microplates, trays, etc. (14 x 5.5") for Incu-Shaker 10L/LR (max. 3)

### Flask & Tube Rack Accessories for MAGic Clamp Platforms

H1000-MR-50	Flask Clamp, 50 ml (H1000-MR: max. 20 / H1010-MR: max. 49)
H1000-MR-125	Flask Clamp, 125 ml (H1000-MR: max. 12 / H1010-MR: max. 36)
H1000-MR-250	Flask Clamp, 250 ml (H1000-MR: max. 8 / H1010-MR: max. 25)
H1000-MR-500	Flask Clamp, 500 ml (H1000-MR: max. 5 / H1010-MR: max. 16)
H1000-MR-1000	Flask Clamp, 1000 ml (H1010-MR: max. 9)
H1000-MR-2000	Flask Clamp, 2000 ml (H1010-MR: max. 5)
H1000-MR-MP	Microplate Clamp, (H1000-MR: max. 4 / H1010-MR: max. 8)
H1000-MR-1550	Tube Rack, 20x50 & 30x15 ml tubes (H1000-MR: max.1 / H1010-MR: max. 4)
H1000-MR-T15	Tube Rack, 32x15 tubes (H1000-MR: max. 2 / H1010-MR: max. 8)
H1000-MR-T50	Tube Rack, 15x50 tubes (H1000-MR: max. 2 / H1010-MR: max. 8)
H1000-MR-T600	Bottle Rack, 4x500/600ml conical bottles (H1000-MR: max. 1 / H1010-MR: max. 2)
H1000-MR-TSR	MAGic Clamp™ tilted holder for 15 ml and 50 ml tube racks
H1000-MR-CMB	Adjustable flask clamp for MAGic clamp platform, accepts 125 ml (max. 36), 250 ml (max. 25) or 500 ml (max. 16)

Additional accessories available. Please visit [www.BenchmarkScientific.com](http://www.BenchmarkScientific.com) for more details.

### Maximum capacity of Erlenmeyer flasks

Flask Size:	Incu-Shaker Mini	Incu-Shaker 10L/LR
50ml	20	49
125ml	12	36
250ml	8	25
500ml	5	16
1L	2	9
2L	0	5



See it on the web!