

## Datenblatt - Data Sheet

*Article:* Threaded glass 16x125 with writing mark

*Article no.:* 90K16125RW

*Material:* **Glass: Borosilikate 5.1**

- Water resistance tested to ISO 719 (at 98 °C): HGB 1
- Alkali resistance tested to ISO 695: class A2
- Acid resistance tested to ISO 12116: S1
- Maximum using temperature long-time load 400°C (\*)
- Maximum using temperature Short-time load 500°C (\*)
- Autoclavable

*Dimension/Standard:* **Thread according to: GPI 15-415**  
**total length H: 125 mm**  
**Outside diameter D: Ø15,75 mm**  
**Wallthickness: 1 mm**

