

# pipetman®

L

VARIABLE VOLUME  
MECHANICAL PIPETTES

PIPETMAN® L multichannel  
models now cover a volume  
range of 0.5 µL to 1200 µL.

## Ultimate Performance

Built for traceability and comfort, PIPETMAN L is designed to increase daily productivity, giving you the ability to pipette longer without fatigue.

## Secure Pipetting

Reduce pipetting errors and avoid accidental volume changes during pipetting cycles with a volume-locking mechanism for improved accuracy and precision.

## Optimized Comfort

Lightweight with light pipetting forces. Right-handed or left-handed? No problem. Adjust the location of the tip ejector to the most comfortable position for you.



 GILSON®



### Classic metal or plastic tip ejector

Choose between a stainless steel tip ejector for more robustness or a plastic tip ejector to avoid corrosion.



### Choose your model

Choose your channel number and volume range. Each ensures consistent volume levels, allowing you to aspirate and dispense your samples with confidence.

**NEW**

PIPETMAN L Single Channel — Variable Volume Models				
Model	PIPETMAN® DIAMOND Tips		Part Number	Volume (µL)
P2L	D10 DL10	DF10ST DFL10ST	FA10001P	0.2 - 2
			FA10001M	
P10L*	D10 DL10	DF10ST DFL10T	FA10002P	1 - 10
			FA10002M	
P20L	D200	DF30ST	FA10003P	2 - 20
			FA10003M	
P100L	D200	DF100ST	FA10004P	10 - 100
			FA10004M	
P200L	D200 D300	DF200ST DF300ST	FA10005P	20 - 200
			FA10005M	
P1000L	D1000 D1200	DF1000ST DF1200ST	FA10006P	100 - 1000
			FA10006M	
P5000L	D5000		FA10007**	500 - 5000
P10mLL	D10mL		FA10008**	1000 - 10000
PIPETMAN L Multichannel				
P8x10L	D10 DL10	DF10ST DFL10ST	FA10013	0.5 - 10
P12x10L			FA10014	
P8x20L	DL10 D200	DFL10ST DF30ST	FA10009	2 - 20
P12x20L			FA10010	
P8x200L	D200 D300	DF200ST DF300ST	FA10011	20 - 200
P12x200L			FA10012	
P8x300L	D200 D300	DF200ST DF300ST	FA10015	20 - 300
P12x300L			FA10016	
P8x1200L	D1200	DF1200ST	FA10039	100 - 1200
P12x1200L			FA10040	

\*P10L model can be used up to 0.5 µL

For a pipette with a plastic tip ejector, the part number ends with the letter P.

For a pipette with a stainless steel tip ejector, the part number ends with the letter M.

PIPETMAN L specifications are downloadable from [www.gilson.com](http://www.gilson.com)

PIPETMAN L single channel models are available in kits.

For even more reproducibility, PIPETMAN L is also available in a fixed version.

[gilson.com/contactus](http://gilson.com/contactus)

**ISO 9001**  
CERTIFIED

LT800565/B | ©2020 Gilson S.A.S.  
All rights reserved. All trademarks  
are the property of Gilson, Inc.  
and its subsidiaries.

**GILSON®**