

COMECTA Sealer "305-C"



FEATURES

Sealer for any type of thermo-plastic material up to 0.4 mm thickness.
 Easy to use: Pressure and release.
 Manual cutting by slip cutting edge.
 Energy saving system by a micro-switch, activated only when the sealing arm is in place.
 Heat impulse for only 0.2 to 1.3 seconds.
 Time controll according to the thickness of plastics to be seal.
 A LED and audible beep are activated when the seal is complete.



MODEL

Part No.	Seal Width mm	Maximum seal length mm	Maximum plastic thickness mm	Seal time seconds	Height / Width / Depth (exterior) cm	Power W	Weight Kg
5800042	5	300	0.4	of 0.2 to 1.3	19 48 8.2	1100	5.2

Supplied complete with 2 heaters, 2 PTFE heater covers and cutting blade.

ADDITIONAL SPARES: Maintenance kit 305-C: 2 heaters, 2 PTFE heater covers and cutting blade Part No. Part No. **5800044**

COMECTA Sealer "455" HIGH THROUGHPUT SEALER.

FEATURES

Ideal for large size samples.
 Sealer for any type of thermo-plastic material up to 0.8 mm thickness.
 Easy to use by pressing a foot pedal which enables to have the hands free in order to manipulate the bag.
 Includes a platform of 45 cm wide x 12 cm depth to support the sample. This platform is adjustable in height up to 19.5 mm to adapt different volumes.
 Energy saving system by a micro-switch, activated only when the sealing arm is in place.
 Heat impulse for only 0.2 to 2.2 seconds.
 Time controll according to the thickness of plastics to be seal.
 A LED and audible beep are activated when the seal is complete.
 Replaceable PTFE anti stick coated heaters.
 The pressure of the pedal can be adjusted.
 Includes a recoil mains cable at the back of the unit.
 All metal robust construction.
 Adjustable base level.



MODEL

Part No.	Seal Width mm	Maximum seal length mm	Maximum plastic thickness mm	Seal time, seconds	Height / Width / Depth (exterior) cm	Power W	Weight Kg
5800047	5	450	0.8	of 0.2 to 2.2	90 54 38	1000	29

Supplied complete with 2 heaters and a fuse.

ADDITIONAL SPARES: Maintenance kit 455: 2 heaters and fuse. Part No. **5800049**

COMECTA Portable sealer "150-C"

FEATURES

Plastic sealer, PE, PP and thermoplastic material such as cellophane, Aluminium covered paper and craft paper up to 0.6 mm thickness.
 Easy to use pressure clamp.
 Parallel seal for both sides of the bag.
 Superior heaters covered in PTFE that produces a parallel hermetic seal.
 Two temperature selection switch 120 °C and 180 °C



MODEL

Part No.	Seal Width mm	Maximum seal length mm	Maximum plastic thickness mm	Height / Width / Depth (exterior) cm	Power W	Weight Kg
5800038	14	150	0.6	9 17 18	50	0.6