

# SEFAR Spécification



SEFAR NITEX 03-100/44 102 cm  
Numéro d' article: 3A03-0100-102-09

Material		PA 6.6.		
	Norme	Valeur	Tolerance	Unité
Laize		102	(+ 1 / - 0)	cm
Epaisseur	ISO 5084	80		µm
Poids		30		g/m2
Ouverture de maille chaîne	ASTM E11	100	(+ 6 / - 6)	µm
Ouverture de maille trame	ASTM E11	100	(+ 6 / - 6)	µm
Nombre de fils chaîne	ASTM E11	66		1/cm
Nombre de fils trame	ASTM E11	66		1/cm
Diamètre du fil chaîne		51		µm
Diamètre du fil trame		51		µm
Surface libre		44		%
Traitement			Stabilized, antistatic	

Sefar provides industry leading, customized products mainly based on monofilament mesh and fabrics , expert services and professional customer support around the world for more than 180 years. Our products are used in a broad spectrum of filtration, separation and dosing applications.

The specifications of our products are designed to meet and exceed the challenging expectations of our customers .

As a result of constant optimization of our manufacturing processes the specifications are subject to slight modification without notice . However, if there are no-change agreements or technical agreements the fabric design will not be changed without prior notification to your company.

Please consult your local Sefar representative to verify that this information remains valid and check the suitability of this product for the targeted application before use.

Please note: This is an automatically generated document . All stated values without indications of tolerances are nominal values, which are not measured. All stated values with indications of tolerances are measured based on a product specific control plan and represent statistical mean values.

Christelle Loé 15/10/2020