

MULTI VORTEX-GENIE® Large Capacity Shaker



“NEXT GENERATION” HIGH CAPACITY VORTEX MIXING

Another revolutionary product from the makers of the Vortex-Genie!

- ⦿ Same true vortexing as with the original Vortex-Genie® 2.
- ⦿ New ADJUSTABLE clamping system accommodates a greater variety of containers, including deep well plates and up to (4) 500mL bottles.
- ⦿ New clamping system allows the user to quickly change from one type of vessel to another.
- ⦿ Digital control and display of speed and time for reproducibility and accuracy, with true speed display.
- ⦿ Programmable gentle ramp up to speed, allows use of open containers.
- ⦿ Durable and heavy zinc die casting with specially designed feet prevents “walking”.
- ⦿ No additional holders or accessories necessary. Racks are included.
- ⦿ May be used in cold rooms or incubators.

Ordering Information

Catalog No.	Description
SI-M236	Multi Vortex-Genie, 120V, 60Hz
SI-M246	Multi Vortex-Genie, 230V, 50Hz, No Plug
SI-M256	Multi Vortex-Genie, 230V, 50Hz, Euro Plug
SI-M266	Multi Vortex-Genie, 230V, 50Hz, British Plug
SI-M276	Multi Vortex-Genie, 230V, 50Hz, Swiss Plug
SI-M296	Multi Vortex-Genie, 240V, 50Hz, Australian Plug
SI-M286	Multi Vortex-Genie, 100V, 50/60Hz

Specifications

Supplied	Two MVG Tube Racks holding up to 12 tubes each of any material up to 29mm dia.
Speed	200 - 1000 RPM (up to 950 RPM for 50Hz models)
Vortexing Orbit	4mm dia. (same as Vortex-Genie 2)
Timer	1-99 minutes or continuous
Dimensions (D x W x H)	310 x 270 x 195mm (12.2 x 10.6 x 7.7in)
Weight	11.3 kgs (25 lbs)



Home of the Multi-Task Genie™ Family
 80 Orville Drive, Suite 102
 Bohemia, NY 11716 U.S.A.
 Phone: (631) 567-4700 • Fax: (631) 567-5896
 Toll Free: 888-850-6208
 Customer Service: custsvc@scientificindustries.com
scientificindustries.com