




## ACC-FLTC-1 / ACC-FLTC-2 withdrawal rods

Version 0

|            |  |  |            |   |            |  |
|------------|--|--|------------|---|------------|--|
|            | Benefits   | Easily connects to type 180 filling hoses of any length. The withdrawal rod with anti-splash avoids any splashing during filling.  |            |   |            |  |
|            | Cryopal Reference  | <table border="1"> <tr> <td>ACC-FLTC-1</td> <td>TC withdrawal rod for Flexible hose 180/180 ND10 LN</td> </tr> <tr> <td>ACC-FLTC-2</td> <td>TC withdrawal rod for Flexible hose 180/180 ND10 LN + Anti-splash plug</td> </tr> </table> | ACC-FLTC-1 | TC withdrawal rod for Flexible hose 180/180 ND10 LN | ACC-FLTC-2 | TC withdrawal rod for Flexible hose 180/180 ND10 LN + Anti-splash plug |
| ACC-FLTC-1 | TC withdrawal rod for Flexible hose 180/180 ND10 LN                    |  |            |   |            |  |
| ACC-FLTC-2 | TC withdrawal rod for Flexible hose 180/180 ND10 LN + Anti-splash plug |  |            |   |            |  |
|            | SAP Reference  | <table border="1"> <tr> <td>116570</td> <td>TC withdrawal rod for Flexible hose 180/180 ND10 LN</td> </tr> <tr> <td>116571</td> <td>TC withdrawal rod for Flexible hose 180/180 ND10 LN + Anti-splash plug</td> </tr> </table>         | 116570     | TC withdrawal rod for Flexible hose 180/180 ND10 LN | 116571     | TC withdrawal rod for Flexible hose 180/180 ND10 LN + Anti-splash plug |
| 116570     | TC withdrawal rod for Flexible hose 180/180 ND10 LN                    |  |            |   |            |  |
| 116571     | TC withdrawal rod for Flexible hose 180/180 ND10 LN + Anti-splash plug |  |            |   |            |  |
|            | Designation  | Withdrawal rod with or without anti-splash for nitrogen hoses type 180/180   |            |   |            |  |
|            | Dimensions / Size  | Total rod length without anti-splash = 450 mm<br>Total length of pipe with anti-splash = 500 mm<br>Fitting for flexible connection = 3/4-16UNF-2A<br>Rod diameter = 12 mm<br>Anti-splash diameter = 38 mm                              |            |   |            |  |
|            | Material   | Rod = Stainless steel<br>Flexible connection = Brass<br>Deflector = Aluminium<br>Handle = Bakelite<br>Anti-splash = Poral sintered metal filter  |            |   |            |  |

|   |          |   |
|---|----------|---|
|   | Use      | From a liquid nitrogen source, via a hose, allows the filling of containers |
|  | Warranty | 2 years   |

|   |                         |  |
|---|-------------------------|--|
|    | Origin                  | France   |
|    | Packaging               | Plastic  |
|   | Weight                  | Withdrawal rod without anti-splash = 0,38 kg<br>Withdrawal rod with anti-splash = 0,60 kg            |
|   | HS Code                 | 84818099   |
|   | Packing                 | Withdrawal rod = = 0,55 x 0,25 x 0,09 M<br>Withdrawal rod with anti-splash = = 0,565 x 0,25 x 0,09 M |
|  | Regulation - Standard   | NA   |
|  | Maintenance<br>Cleaning | NA   |

For any information, feel free to contact us :

 Cryopal  
 Parc Gustave Eiffel - 8, avenue Gutenberg  
 CS10 172 - Bussy Saint-Georges  
 77 607 - Marne La Vallée cedex 3 - France

 00 33 1 64 76 15 00  
 [contact.cryopal@airliquide.com](mailto:contact.cryopal@airliquide.com)  
 <http://www.cryopal.com>