

Shakers

Shaker, microtitre, SS:5 Range

- High speed, small orbiting action – ideal for microtitre plates
- Capacity for four or eight microtitre plates
- Digital selection of speed
- In built digital timer
- Accessories available for mixing microcentrifuge tubes

With the combination of high speed and a tiny orbit the SS:5 range has an ideal action for mixing microtitre plates and microcentrifuge tubes. Microtitre plates are held to the platform by a highly efficient non slip mat. Microtubes can be held via the purpose built accessory racks, available separately.

The SS:5 range has adjustable speed control between 250 and 1250rpm, the speed is shown via the bright LED display and accurately controlled by an encoder. The versatile timer can be set from 1 second to 9 hours. The unit can also be set for continuous operation.

Technical Specification

	SSM5	SSL5
Platform dimensions, mm (w x l)	220 x 220	306 x 306
Number of plate positions	4	8
Speed range, rpm	250 to 1250	250 to 1250
Orbit diameter, mm	1.5	1.5
Maximum load, kg	1	2
Operational temperature range	+4 to +40°C	+4 to +40°C
Maximum permissible humidity	80%	80%
Dimensions, mm (w x d x h)	240 x 300 x 160	360 x 420 x 160
Net weight, kg	5	10
Electrical supply	230V, 50Hz, 50W	230V, 50Hz, 50W
IP Rating	31	31

Ordering Information

Model	Description
SSM5	Shaker, microtitre, mini
SSL5	Shaker, microtitre, labscale
SSM5/1	Tube holder for 1.5ml tubes
SSM5/2	Tube holder for 0.5ml tubes
SSM5/3	Tube holder for 0.2ml tubes



SSM5



SSL5