



Technical data sheet for Dewar flasks made of stainless steel type DSS and GSS

Area of application

- laboratory technique
- medicinal technique
- biotechnology
- storing and company internal short-distance transport for CO₂ and LN₂
- liquid or solid medias and solid matters
- pressure-less space for coolants



Dewar flasks type DSS

Features of performance

- reliably and economically
- nominal capacity from 0,5 to 6 litres
- Dewar flasks with and without grip and handle



Dewar flasks type GSS

Description of Dewar flasks

Types and accessories

- DSS = Dewar flasks from type DSS 1000 with handle
- handle = stainless steel
- lid = polyurethane

- GSS = Dewar flasks with side grip
- GSS = Dewar flasks from type GSS 1000 with handle and side grip
- handle = stainless steel
- Side grip = plastic
- lid = polyurethane

Description of Dewar flask

Material

- Stainless steel

Temperature range

- from -200°C to +150°C, for a short time +200°C
- lid to + 80°C

Pressures range

- Pressure / less

KGW - ISOTHERM


Karlsruher Glastechnisches Werk
76185 Karlsruhe Gablonzerstraße 6
Tel: 0721 95897-0 Fax: 0721 95897-77
E-Mail: info@KGW-ISOTHERM.COM
Internet: www.KGW-ISOTHERM.COM



Technical data sheet for Dewar flasks made of stainless steel type DSS and GSS

Safety advises and regulations

- always wear protective glasses and protective gloves
- national regulations for laboratories
- company- internal regulations
- safety regulations for handling with liquid gases
- ADR regulations



Measurements data

Dewar flasks made of stainless steel, technical specifications								
Type	max. Content	A	B	D	E	Weight	Holding time LN2	Evaporation rate LN2
	ca. [ml]	mm	mm	mm	mm	ca. [kg]	ca. [h]	ca. [L / d]
DSS/GSS 500	500	65	87	180	203	0,6	12	1,0
DSS/GSS 1000	1000	85	107	206	231	0,9	21	0,9
DSS/GSS 1000 W	1000	100	122	157	177	0,7	15	1,6
DSS/GSS 2000	2000	100	122	285	312	1,3	42	1,1
DSS/GSS 3000	3000	185	200	160	190	1,5	22	3,1
DSS/GSS 6000	6000	185	200	270	300	2,2	49	2,9

Article numbers							
Type	Article No.		Type	Article No.		Plug for type	Article No.
GSS 500	2304		DSS 500	2100		DSS/GSS 500	2680
GSS 1000	2300		DSS 1000	2101		DSS/GSS 1000	2681
GSS 1000 W	2301		DSS 1000 W	2102		DSS/GSS 1000 W	2682
GSS 2000	2303		DSS 2000	2103		DSS/GSS 2000	2682
GSS 3000	2302		DSS 3000	2104		DSS/GSS 3000	2683
GSS 6000	2305		DSS 6000	2105		DSS/GSS 6000	2683