



## 1-line display Stopwatch **SPECIAL SWIMMING**

### **3 ATM water resistant :**

- ▶ Resistant to swimming on the surface (without the use of buttons)

### **SPLIT or LAP stopwatch :**

- ▶ SPLIT : Measure the elapsed time from the start
- ▶ LAP : Measure the interval time for each crossing

### **Timer :**

- ▶ Exercise time count down, and overrun count up

#### **Specifications :**

- ▶ 1 line display
- ▶ Capacity : 10h with 1/100 sec resolution
- ▶ Split or Lap stopwatch / 2 memories
- ▶ 10h count down / Counting overrun time
- ▶ Battery A76
- ▶ 3 ATM water resistant