

Flow Rates Peristaltic Pump

Model No. : LabN3-III

Flow Rate : 0.0053-1808mL/min



Single Channel



Dual Channel

Product Features

3.2" color LCD screen display.

Flow rate and motor speed display in same screen.

Timing function, time range 0.1s-9999 hours, can be used for simple dispensing function.

Screen Display



Pump Head



EasyPump Series (Pressure Adjustable)



EasyPump Series (Fixed Pressure)



EasyPump-PPS Series (Pressure Adjustable)



EasyPump-PPS Series (Fixed Pressure)

Pump Head & Flow Rate

Pump Head	Single/Dual Channel	Tubing Wall Thickness(mm)	Pressure Adjustable
EasyPump I	Single Channel	1.6	No
EasyPump II	Single Channel	2.4	No
EasyPump V	Dual Channel	1.6	No

Pump Head	Single/Dual Channel	Tubing Wall Thickness(mm)	Pressure Adjustable
EasyPump III	Single Channel	1.6	Adjustable
EasyPump IV	Single Channel	2.4	Adjustable
EasyPump VI	Dual Channel	1.6	Adjustable



Pump Head	Tubing	ID×Wall thickness(mm)	mL / r	Flow Rate(mL/min) (LabN3-III, 0.1-350rpm)	Tubing Max.Pressure(Mpa)		Weight(kg)
					Intermittent	Continuous	
Single Channel EasyPump I/III	13#	0.8×1.6	0.053	0.0053~19	0.27	0.17	0.6
	14#	1.6×1.6	0.27	0.027~95			
	19#	2.4×1.6	0.55	0.055~193			
	16#	3.1×1.6	0.933	0.093~327	0.24	0.14	
	25#	4.8×1.6	1.967	0.197~688			
	17#	6.4×1.6	3.333	0.333~1167	0.14	0.10	
	18#	7.9×1.6	4.3	0.430~1505	0.10	0.07	
Single Channel EasyPump II/IV	15#	4.8×2.4	1.8	0.180~630	0.27	0.17	
	24#	6.4×2.4	2.733	0.273~957	0.24	0.14	
	35#	7.9×2.4	3.833	0.383~1342			
	36#	9.6×2.4	5.167	0.517~1808			
Dual Channel EasyPump V/VI	13#	0.8×1.6	0.0053	0.0053~19	0.27	0.17	0.6
	14#	1.6×1.6	0.27	0.027~95			
	19#	2.4×1.6	0.55	0.055~193			
	16#	3.1×1.6	0.933	0.093~327	0.24	0.14	
	25#	4.8×1.6	1.967	0.197~688			

Technical Specifications

Flow rate range	0.0053~1808 mL/min	Communication interface	RS232, RS485 support MODBUS protocol (RTU mode)
Speed range	0.1-350rpm		
Speed resolution	0.1rpm	Output interface	Output motor working status (Open-Collector output)
Back suction angle	0-360°		
Testing time range	0.1 s-9999 h	Power supply	AC 220V±10% 50Hz/60Hz (standard)
Motor type	Closed-loop stepper motor		AC 110V±10% 50Hz/60Hz (optional)
Display	3.2" high definition LCD screen	Drive dimension (L×W×H)	259×157×237 mm
Control method	Digital knob and Mechanical keypad		
Keypad lifetime	300,000 times	Drive weight	4.40 kg
External speed control signal	0-5V, 0-10V, 4-20mA for option	Power consumption	<80W
Start/stop, reversing signal	Passive switch signal, such as foot pedal; Active switch signal: 5V-24V universal	Condition temperature	0-40°C
		Relative humidity	<80%

Dimension Drawing (Unit:mm)

