

	Product Specification	Specification Number	5065S-3000
		Revision	02

Part No. 5065S-3000

Description Stainless Telescopic Rods

Material of Construction:
 Tube 316 Stainless Steel
 Clutch PTFE



Minimum Length: 1530mm


Maximum Length: 3020mm

Diameter of Outer Tube: 25mm

Weight: 2.3Kg

Number of Tube Sections: 2

Recommended Storage Conditions: Dry and ambient temperature

Specification Approved By:	Signature: 	Name: Jonathan Fenner Position: Director Date: 5-Feb-15
Page 1 of 1	Sampling Systems Ltd. 4-5 Forge Mills Park, Station Road, Coleshill, Warwickshire. B46 1JH. UK. Tel: +44(0)1675 466992 Fax: +44(0)1675 466994 Email: info@sampling.com Web: www.sampling.com	