



Basic Peristaltic Pump

Model No. : LabM1-III

Flow Rate : 0.0053-775mL/min



Single Channel



Dual Channel

Product Features

3 digital LED display motor speed, mechanical keypad control.

Timing function, the time range of 0.5 seconds -999 seconds can be used as a simple dispensing.

Support RS232 and RS485 communication, Modbus protocol.

Screen Display



Pump Head



EasyPump Series (Pressure Adjustable)



EasyPump Series (Fixed Pressure)



EasyPump-PPS Series (Pressure Adjustable)



EasyPump-PPS Series (Fixed Pressure)

Pump Head & Flow Rate

Pump Head	Single/Dual Channel	Tubing Wall Thickness(mm)	Pressure Adjustable
EasyPump I	Single Channel	1.6	No
EasyPump II	Single Channel	2.4	No
EasyPump V	Dual Channel	1.6	No

Pump Head	Single/Dual Channel	Tubing Wall Thickness(mm)	Pressure Adjustable
EasyPump III	Single Channel	1.6	Adjustable
EasyPump IV	Single Channel	2.4	Adjustable
EasyPump VI	Dual Channel	1.6	Adjustable



Pump Head	Tubing	ID×Wall thickness(mm)	mL / r	Flow Rate(mL/min) (LabM1-III, 0.1-150rpm)	Tubing Max.Pressure(Mpa)		Weight(kg)
					Intermittent	Continuous	
Single Channel EasyPump I/III	13#	0.8×1.6	0.053	0.0053~8	0.27	0.17	0.6
	14#	1.6×1.6	0.27	0.027~41			
	19#	2.4×1.6	0.55	0.055~83			
	16#	3.1×1.6	0.933	0.093~140	0.24	0.14	
	25#	4.8×1.6	1.967	0.197~295			
	17#	6.4×1.6	3.333	0.333~500	0.14	0.10	
	18#	7.9×1.6	4.3	0.430~645	0.10	0.07	
Single Channel EasyPump II/IV	15#	4.8×2.4	1.8	0.180~270	0.27	0.17	
	24#	6.4×2.4	2.733	0.273~410	0.24	0.14	
	35#	7.9×2.4	3.833	0.383~575			
	36#	9.6×2.4	5.167	0.517~775			
Dual Channel EasyPump V/VI	13#	0.8×1.6	0.0053	0.0053~8	0.27	0.17	
	14#	1.6×1.6	0.27	0.027~41			
	19#	2.4×1.6	0.55	0.055~83			
	16#	3.1×1.6	0.933	0.093~140			
	25#	4.8×1.6	1.967	0.197~295	0.24	0.14	

Technical Specifications

Flow rate range	0.0053~775 mL/min	Start/stop, direction signal	Passive switch signal, such as foot pedal; Active switch signal: 5V-24V universal
Speed range	0.1-150rpm		
Speed resolution	0.1rpm when the speed is 0-100rpm,	Communication interface	RS232, RS485 support MODBUS protocol (RTU mode)
	1rpm when the speed is 100-600rpm.		
Testing time range	0.5 s-999s	Power supply	AC 220V±10% 50Hz/60Hz (standard)
Motor type	Closed-loop stepper motor		AC 110V±10% 50Hz/60Hz (optional)
Display	3 digital LED	Drive dimension(L×W×H)	259×157×237 mm
Control method	Mechanical keypad	Drive weight	4.40 kg
Keypad lifetime	300,000 times	Power consumption	<80W
External speed control signal	0-5V, 4-20mA, 0-10V	Condition temperature	0-40°C
		Relative humidity	<80%

Dimension Drawing (Unit:mm)

