

For Microtiter Plates or DeepWells of all familiar brands.
Base of drawers closed. Draw front closed to maximum.

Up to 45 mm plate height • with hand grip

Open Design

Cat. No. **SM45** - x PB V

		3x08	4x08	5x08	6x08	7x08	8x08	
08								398 ⁺ 426
07								348 ⁺ 373
06	on request							299 ⁺ 320
05								249 ⁺ 267
04								200 ⁺ 214
		3x06	4x06	5x06	6x06	7x06	8x06	
		3x05	4x05	5x05	6x05	7x05	8x05	
		3x04	4x04	5x04	6x04	7x04	8x04	
	O = Without Stop	294	380	466	552	638	724	
	M = With	294	380	466	552	638	724	

Closed Design

Cat. No. **SM45** - x HB V

		3x08	4x08	5x08	6x08	7x08	8x08	
08								398 ⁺ 426
07								348 ⁺ 373
06	on request							299 ⁺ 320
05								249 ⁺ 267
04								200 ⁺ 214
		3x06	4x06	5x06	6x06	7x06	8x06	
		3x05	4x05	5x05	6x05	7x05	8x05	
		3x04	4x04	5x04	6x04	7x04	8x04	
	O = Without Stop	304	390	476	562	648	734	
	M = With	304	390	476	562	648	734	

Example: Cat. No. **SM45 - 5 x 05 PBOV**

MT drawer rack for 25 microtiter plates **without** safety stop.
Dimensions: WxDxH = 137x466x249 mm

Example: Cat. No. **SM45 - 4 x 06 HB MV**

MT drawer rack for 24 microtiter plates **with** safety stop.
Dimensions: WxDxH = 137x390x320 mm

Up to 53 mm plate height • with hand grip

Open Design

Cat. No. **SM53** - x PB V

		3x07	4x07	5x07	6x07	7x07	8x07	
07								404 ⁺ 429
06								347 ⁺ 368
05	on request							289 ⁺ 307
04								232 ⁺ 246
03								174 ⁺ 185
		3x06	4x06	5x06	6x06	7x06	8x06	
		3x05	4x05	5x05	6x05	7x05	8x05	
		3x04	4x04	5x04	6x04	7x04	8x04	
		3x03	4x03	5x03	6x03	7x03	8x03	
	O = Without Stop	294	380	466	552	638	724	
	M = With	294	380	466	552	638	724	

Closed Design

Cat. No. **SM53** - x HB V

		3x07	4x07	5x07	6x07	7x07	8x07	
07								404 ⁺ 429
06								347 ⁺ 368
05	on request							289 ⁺ 307
04								232 ⁺ 246
03								174 ⁺ 185
		3x06	4x06	5x06	6x06	7x06	8x06	
		3x05	4x05	5x05	6x05	7x05	8x05	
		3x04	4x04	5x04	6x04	7x04	8x04	
		3x03	4x03	5x03	6x03	7x03	8x03	
	O = Without Stop	304	390	476	562	648	734	
	M = With	304	390	476	562	648	734	

Up to 58 mm plate height • with hand grip

Open Design

Cat. No. **SM58** - x PB V

		3x06	4x06	5x06	6x06	7x06	8x06	
06								377 ⁺ 398
05								314 ⁺ 332
04	on request							252 ⁺ 266
03								189 ⁺ 200
		3x05	4x05	5x05	6x05	7x05	8x05	
		3x04	4x04	5x04	6x04	7x04	8x04	
		3x03	4x03	5x03	6x03	7x03	8x03	
	O = Without Stop	294	380	466	552	638	724	
	M = With	294	380	466	552	638	724	

Closed Design

Cat. No. **SM58** - x HB V

		3x06	4x06	5x06	6x06	7x06	8x06	
06								377 ⁺ 398
05								314 ⁺ 332
04	on request							252 ⁺ 266
03								189 ⁺ 200
		3x05	4x05	5x05	6x05	7x05	8x05	
		3x04	4x04	5x04	6x04	7x04	8x04	
		3x03	4x03	5x03	6x03	7x03	8x03	
	O = Without Stop	304	390	476	562	648	734	
	M = With	304	390	476	562	648	734	