

schuett petriturn-E

Turntables for Petri dishes

- electrically driven
- with sensor
- body from stainless-steel
- handling of the turntable contactless by sensor
- for Petri dishes up to Ø 100 mm (to Ø 150 mm optional)

For uniform plating of liquids on agar-surfaces in Petri dishes

Continuously adjustable, constant speed of 10-100 rpm and continuously adjustable operating time of 3 s to 2 min or permanent running.

Optional connection of a foot-switch.

Technical Data

Dimensions (Ø x h)	160 x 70 mm
Weight:	approx. 1 kg
Wall power supply:	12 V DC, 5 VA
Speed continuously variable adjustable	10-100 rpm
Operating time variable adjustable	3 s - 2 min / permanent running

Turntables for Petri dishes of other diameters available on request.

Ordering Information

Type	Cat.-No.
schuett petriturn-E, electrically driven, 230 V	3.361 252
schuett petriturn-E, electrically driven, 115 V	3.361 262
Accessories	
Foot-switch for schuett petriturn-E	3.361 302
Turntable-attachment for Petri dishes up to Ø 150 mm	3.361 402
Inoculating hook	
Inoculating hook made of stainless steel (Drigalski-hook)	3.362 152
Inoculating hook made of glass (Drigalski-hook)	3.362 162