

TECHNICAL FEATURE

7NK 90NHDP 01 905



The :

- Ergonomy and design
- Eliminates the fatigue
- Polyvalent
- Auto-adaptive
- Without staples nor seams
- Abrasion-resistant

KONCEPT SEATS / POLYURETHANE

Black steel, 5-branch, scuff-resistant, reinforced base with articulated glides

Black gas-lift column with height adjustment from 610 to 855 mm

and shock absorber

Height adjustable aluminium foot-ring

Deformable seat in black KANGO soft polyurethane, tilted of 2° forward

Assembly on silentbloc. Auto-adaptive system in the movements of the user