



S 18 N - 10 G Dispersing element

Suitable for dispersing instrument T 18 digital
 Working range: 1 - 100 ml
 Stator diameter: 10 mm
 Immersion depth: 25 - 70 mm
 Materials in contact with medium: PTFE, AISI 316L
 Suitable for solvents
 Max. temperature: 180 °C
 Sterilization methods: all methods

Technical Data	
Volume range min. (H2O) [l]	0.001
Volume range max. (H2O) [l]	0.1
Stator diameter [mm]	10
Rotor diameter [mm]	7.5
Gap between rotor and stator [mm]	0.35
allowable Speed max. [rpm]	25000
Circumferential speed max. [m/s]	9.8
Immersion depth min. [mm]	25
Immersion depth max. [mm]	70
Shaft length [mm]	108
Material in contact with medium	PTFE, AISI 316L
pH min.	2
pH max.	13
Suitable for solvents	yes
Suitable for abrasive substances	yes
Working temperature max. [°C]	180
Sterilization methods	all methods
Ultimate fineness, suspensions min. [µm]	10
Ultimate fineness, suspensions max. [µm]	50
Ultimate fineness, emulsions min. [µm]	1
Ultimate fineness, emulsions max. [µm]	10
Ident. No.	000L004639