



S 18 D - 14 G - KS Dispersing element (12 Pc)

Suitable for dispersing instrument T 18 digital

Working range: 10 - 500 ml

Stator diameter: 14 mm

Immersion depth: 15 - 85 mm

Materials in contact with medium: Polycarbonat (PC), Polyetheretherketon (PEEK)

Max. temperature: 100 °C

Sterilization methods: autoclavable

Plastic materials used approved by FDA.

Packaging unit: 12 pieces

Technical Data

Volume range min. (H2O) [l]	0.01
Volume range max. (H2O) [l]	0.5
Stator diameter [mm]	14
Rotor diameter [mm]	9.5
Circumferential speed max. [m/s]	12
Immersion depth min. [mm]	15
Immersion depth max. [mm]	85
Shaft length [mm]	150
Material in contact with medium	Polycarbonat (PC), Polyetheretherketon (PEEK)
Working temperature max. [°C]	100
Sterilization methods	autoclavable

Ident. No. 0003452300