



### S 25 D - 10 G - KS Dispersing element (12 Pc)

Suitable for dispersing instrument T 25 digital

Working range: 10 - 100 ml

Stator diameter: 10 mm

Immersion depth: 15 - 85 mm

Materials in contact with medium: Polycarbonat (PC), Polyetheretherketon (PEEK)

Max. temperature: 100 °C

Sterilization methods: autoclavable

Plastic materials used approved by FDA.

Packaging unit: 12 pieces

#### Technical Data

Volume range min. (H2O) [l]	0.01
Volume range max. (H2O) [l]	0.1
Stator diameter [mm]	10
Rotor diameter [mm]	6.75
Circumferential speed max. [m/s]	8.5
Immersion depth min. [mm]	15
Immersion depth max. [mm]	85
Shaft length [mm]	150
Material in contact with medium	Polycarbonat (PC), Polyetheretherketon (PEEK)
Working temperature max. [°C]	100
Sterilization methods	autoclavable

**Ident. No.** 0003452200