



S 10 N - 8 G Dispersing element

Suitable for dispersing instrument T 10 basic and T 10 standard

Working range: 1 - 50 ml

Stator diameter: 8 mm

Immersion depth: 20 - 95 mm

Materials in contact with medium: PTFE, AISI 316L

Suitable for solvents: yes

Max. temperature: 180 °C

Sterilization methods: all methods

Technical Data

Volume range min. (H ₂ O) [l]	0.001
Volume range max. (H ₂ O) [l]	0.050
Stator diameter [mm]	8
Rotor diameter [mm]	6.1
Gap between rotor and stator [mm]	0.25
Circumferential speed max. [m/s]	9.6
Immersion depth min. [mm]	20
Immersion depth max. [mm]	95
Shaft length [mm]	115
Material in contact with medium	PTFE, AISI 316L
pH min.	2
pH max.	13
Suitable for solvents	yes
Suitable for abrasive substances	yes
Working temperature max. [°C]	180
Sterilization methods	all methods
Ultimate fineness, suspensions min. [µm]	5
Ultimate fineness, suspensions max. [µm]	25
Ultimate fineness, emulsions min. [µm]	1
Ultimate fineness, emulsions max. [µm]	10
Ident. No.	0003305500