



S 10 D - 7G - KS - 65 Dispersing element (24 pcs)

Plastic dispersing element for T 10 basic and T 10 standard
 Working range: 1 - 40 ml
 Diameter: 7 mm
 Immersion depth: 20 - 90 mm
 Material: PC, PSU
 Max. temperature: 100°C
 Autoclavable

Technical Data

Volume range min. (H2O) [l]	0.001
Volume range max. (H2O) [l]	0.020
Stator diameter [mm]	7
Rotor diameter [mm]	4.8
Circumferential speed max. [m/s]	7.5
Immersion depth min. [mm]	20
Immersion depth max. [mm]	45
Shaft length [mm]	65
Material in contact with medium	Polycarbonat (PC), Polysulfon (PSU)
Working temperature max. [°C]	100
Sterilization methods	autoclavable
Ident. No.	0020002076