



C-MAG HP 4

Hotplate made of ceramic glass which offers excellent chemical resistance.

- Fixed safety circuit of 550 °C
- Hot Top indicator >> hot surface warning to prevent burns!
- Exact temperature setting via digital display (LED)
- Digital error code display
- Elevated control panel for protection against leaking liquids

Accessories: H 16 V Support rod, C-MAG Adapter, LABLIFT m

Technical Data	
Number of heating points	1
Heat output [W]	250
Heating temperature range [°C]	50 - 500
Heat control	LED
Set temperature resolution [±K]	10
Volume max. [l]	5
Heating rate heating plate [K/min]	2.5
Set-up plate material	ceramic
Set-up plate dimensions [mm]	100 x 100
Dimensions (W x H x D) [mm]	150 x 105 x 260
Weight [kg]	3
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 21
Voltage [V]	230 / 120 / 100
Frequency [Hz]	50/60
Power input [W]	255
Ident. No.	0003581600