



### Vortex 1

A new attractively designed test tube shaker with touch function and infinitely adjustable speed from 1000 – 2800 rpm.

Designed for mixing small test samples.

- Small, compact and reliable
- For small containers up to 30 mm in diameter, e.g. test tubes, centrifuge tubes, Eppendorf beakers
- Infinitely adjustable speed from 1000 – 2800 rpm
- Excellent mixing action
- The upper casing and the test tube surface are made from inert plastic. The bottom section is a coated, zinc die-casting
- Includes light 12 V power pack

#### Données techniques

Type de mouvement	orbitale
Agitateurs orbitaux [mm]	4.5
Capacité admissible (support inclus) [kg]	0.1
Puissance du moteur absorbée [W]	1.2
Puissance du moteur débitée [W]	0.8
Durée de fonctionnement admissible [%]	100
Vitesse min. réglable [rpm]	1000
Vitesse max. [rpm]	2800
Affichage de la vitesse	aucun
Minuterie	non
Affichage de la minuterie	aucun
Fonction " touch"	oui
Plateau d'agitation fixe	non
Travailler avec microtitration	non
Dimensions (L x P x H) [mm]	95 x 70 x 110
Poids [kg]	0.55
Plage de température du milieu admise [°C]	5 - 40
Humidité relative admissible [%]	80
Protection selon DIN EN 60529	IP 40
Tension [V]	100 - 240
Fréquence [Hz]	50/60
Puissance absorbée de l'appareil [W]	30
<b>Ident. N°.</b>	<b>0004047700</b>