



KS 3000 ic control

Innovative incubator shaker design allowing unattended* operation in a temperature-controlled environment.

- Large LED display for speed and time settings
- Controls with antimicrobial coating for reduction of bacteria
- Integrated PID temperature control (use of two PT 1000 temperature sensors)
- Junction box in the workspace for connection of an additional temperature sensor e.g. PT 1000.60
- Electronic temperature and speed control
- Electronic timer switch: 0 - 999 h (set by the minute or by the hour)
- Optional built-in cooler for connection to an external cooling unit e.g. KV 600
- Unit switches off automatically if disturbed
- Unit stops automatically when hood is lifted
- Collecting tray with drain hose on rear of unit
- Simple operation
- All functions can be controlled and documented with labworldsoft®
- Attachments are not included in delivery, please order separately

Shaking movement: orbital

Orbital diameter: 20 mm

Max. shaking weight (with attachment): 7,5 kg

Infinitely adjustable speed range: 10 - 500 rpm

Heat output: 1.000 W

Temperature range: RT + 5 °C to 80 °C

Accessories: STICKMAX, AS 260.2 Fixing clip attachment, AS 260.3 Dish attachment, AS 260.5 Separating funnel attachment, AS 1.61 Clamping roll, AS 1.60 Basic holder, AS 260.1 Universal attachment, RC 2 basic, RC 2 control, PC 1.1 Cable, labworldsoft®

Technical Data

Type of movement	orbital
Shaker diameter [mm]	20
Permissible shaking weight (incl. attachment) [kg]	7.5
Motor rating input [W]	45
Motor rating output [W]	10
Permissible ON time [%]	100
Speed min (adjustable) [rpm]	10
Speed range [rpm]	10 - 500
Speed display	LED
Speed deviation [%]	1
Speed control	1 RPM steps
Timer	yes
Timer display	7 segment LED
Time setting min. [s]	1

Time setting range [min]	1 - 59940
Operating mode	timer and continuous operation
Touch function	no
Shaking table lock	no
Working with microtiter plates	no
Heat output [W]	1000
Set temperature resolution [±K]	0.1
Control accuracy with sensor (1 vessel 0.5 L H ₂ O, RT 22°C, T=37°C) [±K]	0.5
Temperature display	yes
Temperature range (inlet T>3°C) [°C]	room temp. - 10° - 80°
connections for external cooling	yes
embedded cooling coil	yes
embedded cooling unit	no
Operating area inner chamber [mm]	330 x 330 x 258
Total volume inner chamber [l]	50
Raw material housing	Sheet metal powder coat
Raw material hood	PMMA
Raw material front foil	polyester
Raw material front panel	ABS painted
Temperature stability (1 vessel 0.5 L, RT 25°C, T=37°C) [±K]	0.05
Temperature homogeneity (5 vessel 0.5 L; RT 25°C, T=37°C) [±K]	0.5
Height with open hood [mm]	875
Dimensions (W x H x D) [mm]	465 x 430 x 695
Weight [kg]	37
Permissible ambient temperature [°C]	15 - 32
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 30
RS 232 interface	yes
USB interface	yes
Voltage [V]	230 / 115 / 100
Frequency [Hz]	50/60
Power input [W]	1120
Ident. No.	0003940100