


Data Sheet

Mixing / Magnetic Stirrers



RET control-visc

PATENTED WORLD FIRST: Safety magnetic stirrer with heating and integrated balance. Clear, multilingual TFT display makes it easy to set all parameters. Integrated temperature control feature enables connection of a temperature probe, placed directly in the medium, to control medium temperature with a high degree of precision. PT 100 temperature sensor is included. The stainless steel composite hot plate, reaching a temperature of 340 °C, enables rapid heating. RS 232 and USB interfaces enable pc control of the magnetic stirrer and documentation of all test parameters. "Lock" function prevents inadvertent changes of speed and temperature settings. As a safety feature, the current temperature is displayed when the unit is switched off but surface is still hot. Below 50 °C the display turns off automatically.

- BNC socket for connection of a pH electrode
- Adjustable temperature control mode: rapid heating and very accurate temperature control
- Dual sensor for simultaneous control of heat transfer fluid temperature and medium temperature
- Timer and countdown functions
- Display of viscosity change trend
- Detached magnet detection
- Intermittent operation
- Several modes of operation available
- Safety circuit adjustable from 50 to 380°
- Transparent protective cover included
- Error code display for easy troubleshooting
- Exact temperature and speed adjustment by means of digital display; even when function switched off
- Suitable for unsupervised operation
- Sealed casing (IP 42) ensures a long service life

Accessories: PT 100.70 Temperature sensor, PT 1000.50 Temperature sensor, PT 100.51 Temperature sensor, PT 1000.51 Temperature sensor, PT 100.53 Temperature sensor, coated, PT 1000.80 Temperature sensor, stainless steel, PT 1000.90 Temperature sensor, coated, H 16 V Support rod, H 16.3 Extension, H 44 Boss head clamp, H 38 Holding rod, H 104 Cover for RET control, H 29 Oil bath attachment, H 30 Oil bath attachment, H 1000, H 1500, H 3000, H 5000, H 8000, IKAFLON® 110 Magnetic stirring bar, IKAFLON® 155 Magnetic stirring bar, IKAFLON® 10 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 15 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 40 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 50 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 80 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® glass 25 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® glass 30 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® glass 40 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® glass 50 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) power SmSo PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) power SmSo PTFE-coated Magnetic stirring bars, IKAFLON® 50 Set (5 Pcs) power SmSo PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 40 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 50 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 35 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 40 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 50 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 60 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 70 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 10 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 38 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 37 Set (5 Pcs) bone PTFE-coated Magnetic stirring bars, IKAFLON® 54 Set (5 Pcs) bone PTFE-coated Magnetic stirring bars, TRIKA® 25 Set (5 Pcs) PTFE-coated Magnetic stirring bars, TRIKA® 35 Set (5 Pcs) PTFE-coated Magnetic stirring bars, TRIKA® 55 Set (5 Pcs)

PTFE-coated Magnetic stirring bars, TRIKA® 80 Set (5 Pcs) PTFE-coated Magnetic stirring bars, IKAFLON® 67 (1 Pc) beaker PTFE-coated Magnetic stirring bars, IKAFLON® 74 (1 Pc) beaker PTFE-coated Magnetic stirring bars, IKAFLON® 103 (1 Pc) beaker PTFE-coated Magnetic stirring bars, IKAFLON® 125 (1 Pc) beaker PTFE-coated Magnetic stirring bars, IKAFLON® 9 Set (5 Pcs) crown PTFE-coated Magnetic stirring bars, RS 1 Set of magnetic stirring bars, RS 2 Set of magnetic stirring bars, RSE Stirring bar remover, H 11 Mains cable Euro plug, H 135.10 Square carrier without handle, H 135.11 Square carrier with handle, H 135.101 Block 16 x 4 ml, H 135.102 Block 16 x 8 ml, H 135.103 Block 9 x 16 ml, H 135.104 Block 4 x 20 ml, H 135.105 Block 4 x 30 ml, H 135.106 Block 4 x 40 ml, H 135.107 Block 100 ml, H 135.108 Block 250 ml, H 135.20 Flask carrier 100 ml without handle, H 135.21 Flask carrier 100 ml with handle, H 135.201 Flask inlay 10 ml, H 135.202 Flask inlay 25 ml, H 135.203 Flask inlay 50 ml, H 135.25 Flask carrier 250 ml without handle, H 135.26 Flask carrier 250 ml with handle, H 135.30 Flask carrier 500 ml without handle, H 135.31 Flask carrier 500 ml with handle, H 135.301 Flask inlay 100 ml, H 135.302 Flask inlay 250 ml, H 135.40 Flask carrier 1000 ml without handle, H 135.41 Flask carrier 1000 ml with handle, H 135.401 Flask inlay 500 ml, H 135.50 Flask carrier 2000 ml without handle, H 135.51 Flask carrier 2000 ml with handle, H 135.501 Flask inlay 1000 ml, LABLIFT m, labworldsoft®, PC 1.1 Cable, BC 1000 Beaker cap, HG 600 Heating jacket, HG 1000 Heating jacket

Technical Data	
Number of stirring positions	1
Stirring quantity max. per stirring position (H2O) [l]	20
Motor rating output [W]	9
Direction of rotation	right
Speed display set-value	TFT
Speed display actual-value	TFT
Speed control	Turning knob
Speed range [rpm]	50 - 1700
Setting accuracy speed [rpm]	10
Stirring bar length min. [mm]	20
Stirring bar length max. [mm]	80
Self-heating of the hotplate by max. stirring (RT:22°C/duration:1h) [+K]	28
Heat output [W]	600
Temperature display set-value	TFT
Temperature display actual-value	TFT
Temperature unit	°C / °F
Heating temperature range [°C]	Room temp. + device self heating - 340
Heat control	Turning knob
Temperature setting range min. [°C]	0
Temperature setting range max. [°C]	340
Temperature setting resolution of heating plate [K]	0.1
Connection for ext. temperature sensor	PT100/PT1000 (dual sensor)
Characteristics in the medium with temperature sensor	1l M50 Oil at H1500
Temperature medium max. [°C]	270
Heating rate medium [K/min]	7
Temperature setting resolution of medium [K]	0.1
Adjustable safety circuit min. [°C]	50
Adjustable safety circuit max. [°C]	380
Set-up plate material	stainless steel 1.4301
Set-up plate dimensions [mm]	Ø 135
Automatic reverse rotation	no
Intermittend mode	yes
Viscosity trend measurement	yes
Break detection stirring bar	yes
Timer	yes
pH measurement	yes
Graph function	yes
Programs	yes
Sensor in medium detection (Error 5)	yes
Weighing function	yes
Weighing range [g]	10-5000
Weighing accuracy	<500g : +/-1g , >500g: +/-5g
Load capacity weighing function max. [kg]	5
Dimensions (W x H x D) [mm]	160 x 85 x 270
Weight [kg]	2.7
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 42
RS 232 interface	yes
USB interface	yes
Analog output	no
Voltage [V]	220 - 240 / 115 / 100
Frequency [Hz]	50/60
Power input [W]	650
Ident. No.	0005020000