

Data Sheet

Mixing / Magnetic Stirrers



RT 15

15-position digital magnetic hotplate stirrer, designed for synchronous heating and stirring. The magnetic coil technology provides noiseless and consistent stirring on all positions. The surface temperature is infinitely adjustable up to 120 °C, producing a maximum medium temperature of 70 °C (depending on the used vessel). Speed remains constant, even when load changes.

- Homogeneous temperature distribution across the heating plate
- Adjustable reverse operation
- Eco-mode for a low self-warming of the surface
- Wear free magnetic coils
- Error code display
- Easy operation with touch keypad
- Suitable for continuous operation
- Speed range: 0 - 1000 rpm

Accessories: IKAFLON® 10 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 15 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® glass 25 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® glass 30 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) power SmSo PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) power SmSo PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars.

Technical Data

Number of stirring positions	15
Stirring position distance [mm]	90
Speed deviation of individual stirring positions [%]	0
Stirring quantity max. per stirring position (H ₂ O) [l]	0.4
Speed control	10 RPM Steps
Speed range [rpm]	0 - 1000
Stirring bar length min. [mm]	25
Stirring bar length max. [mm]	30
Heat output [W]	580
Heating temperature range [°C]	Room temp. - 120
Heat control	LED
Heating rate heating plate [K/min]	3
Adjustable safety circuit min. [°C]	50
Adjustable safety circuit max. [°C]	150
Set-up plate material	Aluminium alloy
Set-up plate dimensions [mm]	270 x 495
Dimensions (W x H x D) [mm]	280 x 60 x 610
Weight [kg]	10.5
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 40
Voltage [V]	230 / 115 / 100
Frequency [Hz]	50/60
Power input [W]	620
Ident. No.	0003692600

stirring bars, IKAFLON® 20 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 10 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 9 Set (5 Pcs) crown PTFE-coated Magnetic stirring bars, TRIKA® 25 Set (5 Pcs) PTFE-coated Magnetic stirring bars, H 11 Mains cable Euro plug, H 11 Mains cable CH plug, RSE Stirring bar remover, BC 1000 Beaker cap, H 11 Mains cable UK plug, H 11 Mains cable USA plug

DOMINIQUE DUTSCHER SAS