

## Data Sheet

Mixing / Magnetic Stirrers



## RO 5

5-position digital magnetic stirrer without heating, designed for synchronous stirring. The magnetic coil technology provides noiseless and consistent stirring on all positions. Speed remains constant, even when load changes. The closed and compact design allows easy cleaning and protects the equipment against the penetration of liquids. Additionally, a removable transparent anti-slip mat is included.

- Adjustable reverse operation
- Wear free magnetic coils
- Error code display
- Easy operation with touch keypad
- Suitable for continuous operation
- Speed range: 0 - 1200 rpm

Accessories: IKAFLON® 10 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 15 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) round PTFE-coated Magnetic stirring bars, IKAFLON® glass 25 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® glass 30 Set (5 Pcs) round Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) power SmSo PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) power SmSo PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) slide

### Technical Data

Number of stirring positions	5
Stirring position distance [mm]	90
Speed deviation of individual stirring positions [%]	0
Stirring quantity max. per stirring position (H <sub>2</sub> O) [l]	0.4
Speed control	10 RPM Steps
Speed range [rpm]	0 - 1200
Stirring bar length min. [mm]	25
Stirring bar length max. [mm]	30
Set-up plate material	stainless steel 1.4301
Set-up plate dimensions [mm]	120 x 470
Dimensions (W x H x D) [mm]	120 x 60 x 570
Weight [kg]	3
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 40
Voltage [V]	100 - 240
Frequency [Hz]	50/60
Power input [W]	13
DC Voltage [V=]	24
Current consumption [mA]	500
<b>Ident. No.</b>	<b>0003690500</b>

round PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) slide round PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) ellipse PTFE-coated Magnetic stirring bars, IKAFLON® 10 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 20 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 25 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 30 Set (5 Pcs) cross PTFE-coated Magnetic stirring bars, IKAFLON® 9 Set (5 Pcs) crown PTFE-coated Magnetic stirring bars, TRIKA® 25 Set (5 Pcs) PTFE-coated Magnetic stirring bars, H 11 Mains cable Euro plug, H 11 Mains cable CH plug, RSE Stirring bar remover, BC 1000 Beaker cap, H 11 Mains cable UK plug, H 11 Mains cable USA plug

DOMINIQUE DUTSCHER SAS